# **Product datasheet**

Specifications





# DIGILINK solid cable - category 5e - SFTP - 4 pair- 305 m

DCECASTP4P3X

() Discontinued on: 21-Oct-2021

#### ① Discontinued

#### Main

Range	Digilink
Product Name	Digilink E400
Product Or Component Type	Copper cable
Device Application	Transmission
Cable Shielding Type	S/FTP
Communication Network Category	5e
Colour Tint	Grey

### Complementary

Type Of Cable	4 twisted pair cables
Conductor Material	Copper
Input Impedance	100 Ohm (+/- 6) at 1100 MHz
Dc Resistance	72 Ohm per 1 km
[Ue] Rated Operational Voltage	72 V DC (maximum)
Insulation Resistance	>= 500 MOhm/km 1 km 500 V DC
Nominal Velocity Propagation	69 %
Cable Outer Diameter	6 mm
Cable Length	305 m
Awg Gauge	AWG 24
Material	PVC (polyvinyl chloride): jacket

#### Environment

Product Certifications	ETL verified
Standards	ANSI/TIA/EIA-568-C.2 UL 94 V0 Class D ISO/IEC 11801

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	4 cm

Package 1 Length	4 cm
Package 1 Weight	10.75 g

Life Is On Schneider

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations