



Logic controller, Modicon M241, 24 IO transistor NPN

TM241C24U

Main

| Range Of Product | Modicon M241 |
|---------------------------|--|
| Product Or Component Type | Logic controller |
| [Us] Rated Supply Voltage | 24 V DC |
| Discrete Input Number | 14, discrete input 8 fast input conforming to IEC 61131-2 Type 1 |
| Discrete Output Type | Transistor |
| Discrete Output Number | 10 transistor 4 fast output |
| Discrete Output Voltage | 24 V DC for transistor output |
| Discrete Output Current | 0.5 A for transistor output (Q0Q9) 0.1 A for fast output (PTO mode) (Q0Q3) |

Complementary

| Discrete I/O Number | 24 |
|---|--|
| Maximum Number Of I/O Expansion Module | 7 (local I/O-Architecture) 14 (remote I/O-Architecture) |
| Supply Voltage Limits | 20.428.8 V |
| Inrush Current | 50 A |
| Power Consumption In W | 32.640.4 W (with max number of I/O expansion module) |
| Discrete Input Logic | Sink or source |
| Discrete Input Voltage | 24 V |
| Discrete Input Voltage Type | DC |
| Voltage State 1 Guaranteed | >= 15 V for input |
| Voltage State 0 Guaranteed | <= 5 V for input |
| Discrete Input Current | 5 mA for input 10.7 mA for fast input |
| Input Impedance | 4.7 kOhm for input 2.81 kOhm for fast input |
| Response Time | 50 μs turn-on, 10113 terminal(s) for input 50 μs turn-off, 10113 terminal(s) for input <= 2 μs turn-on, 1017 terminal(s) for fast input <= 2 μs turn-off, 1017 terminal(s) for fast input <= 34 μs turn-on, Q0Q9 terminal(s) for output <= 250 μs turn-off, Q0Q9 terminal(s) for output <= 2 μs turn-on, Q0Q3 terminal(s) for fast output <= 2 μs turn-off, Q0Q3 terminal(s) for fast output |

| Configurable Filtering Time | 1 µs for fast input 12 ms for fast input 0 ms for input 1 ms for input 4 ms for input 12 ms for input |
|--------------------------------------|--|
| Discrete Output Logic | Negative logic (sink) |
| Output Voltage Limits | 30 V DC |
| Maximum Current Per Output Common | 2 A with Q0Q3 for fast output 2 A with Q4Q7 for output 1 A with Q8Q9 for output |
| Maximum Output Frequency | 20 kHz for fast output (PWM mode) 100 kHz for fast output (PLS mode) 1 kHz for output |
| Accuracy | +/- 0.1 % at 0.020.1 kHz for fast output +/- 1 % at 0.11 kHz for fast output |
| Maximum Leakage Current | 5 μA for output |
| Maximum Voltage Drop | <1 V |
| Maximum Tungsten Load | <2.4 W |
| Protection Type | Short-circuit protection Short-circuit and overload protection with automatic reset Reverse polarity protection for fast output |
| Reset Time | 10 ms automatic reset output 12 s automatic reset fast output |
| Memory Capacity | 64 MB for system memory RAM |
| Data Backed Up | 128 MB built-in flash memory for backup of user programs |
| Data Storage Equipment | <= 16 GB SD card (optional) |
| Battery Type | BR2032 lithium non-rechargeable, battery life: 4 year(s) |
| Backup Time | 2 years at 25 °C |
| Execution Time For 1 Kinstruction | 0.3 ms for event and periodic task 0.7 ms for other instruction |
| Application Structure | 4 cyclic master tasks 8 external event tasks 8 event tasks 3 cyclic master tasks + 1 freewheeling task |
| Realtime Clock | With |
| Clock Drift | <= 60 s/month at 25 °C |
| Positioning Functions | PTO function 4 channel(s) (positioning frequency: 100 kHz) PTO function 4 channel(s) for transistor output (positioning frequency: 1 kHz) |
| Counting Input Number | 4 fast input (HSC mode) at 200 kHz 14 standard input at 1 kHz |
| Control Signal Type | A/B at 100 kHz for fast input (HSC mode) Pulse/direction at 200 kHz for fast input (HSC mode) Single phase at 200 kHz for fast input (HSC mode) |
| Integrated Connection Type | Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface Non isolated serial link serial 2 with removable screw terminal block connector and RS485 interface USB port with mini B USB 2.0 connector |
| Supply | (serial 1)serial link supply: 5 V, <200 mA |
| Transmission Rate | 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for bus length of 3 m for USB |
| Communication Port Protocol | Non isolated serial link: Modbus master/slave |

| Local Signalling | 1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (red) for I/O error (I/O) |
|--|--|
| | 1 LED (green) for SD card access (SD) 1 LED (red) for BAT |
| | 1 LED (green) for SL1 |
| | 1 LED (green) for SL2 1 LED (red) for bus fault on TM4 (TM4) |
| | 1 LED per channel (green) for I/O state |
| Electrical Connection | removable screw terminal blockfor inputs and outputs (pitch 5.08 mm) removable screw terminal blockfor connecting the 24 V DC power supply (pitch 5.08 mm) |
| Maximum Cable Distance | Unshielded cable: <50 m for input |
| Between Devices | Shielded cable: <10 m for fast input Unshielded cable: <50 m for output |
| | Shielded cable: <3 m for fast output |
| Insulation | Between supply and internal logic at 500 V AC |
| | Non-insulated between supply and ground |
| | Between input and internal logic at 500 V AC Non-insulated between inputs |
| | Between fast input and internal logic at 500 V AC |
| | Between output and internal logic at 500 V AC Non-insulated between outputs |
| | Between fast output and internal logic at 500 V AC |
| Marking | CE |
| Surge Withstand | 1 kV power lines (DC) common mode conforming to IEC 61000-4-5 |
| _ | 1 kV shielded cable common mode conforming to IEC 61000-4-5 |
| | 0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5 |
| | 1 kV relay output differential mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5 |
| | 1 kV transistor output common mode conforming to IEC 61000-4-5 |
| Mounting Support | Top hat type TH35-15 rail conforming to IEC 60715 |
| | Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit |
| Height | 90 mm |
| Depth | 95 mm |
| Width | 150 mm |
| Net Weight | 0.53 kg |
| Environment | |
| Standards | ANSI/ISA 12-12-01 |
| | CSA C22.2 No 142 |
| | CSA C22.2 No 213 |
| | IEC 61131-2:2007 Marine specification (LR, ABS, DNV, GL) |
| | UL 508 |
| Product Certifications | RCM |
| | cULus |
| | CE UKCA |
| | DNV-GL |
| | ABS LR |
| | |
| Resistance To Electrostatic Discharge | 8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2 |
| Resistance To Electromagnetic | 10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 |
| Fields | 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3 |
| Resistance To Fast Transients | 2 kV (power lines) conforming to IEC 61000-4-4 |
| | 1 kV (serial link) conforming to IEC 61000-4-4 |
| | 1 kV (input) conforming to IEC 61000-4-4 1 kV (transistor output) conforming to IEC 61000-4-4 |
| | . A. (Walliolisto) outputy conformility to ILO 01000-4-4 |

| Resistance To Conducted Disturbances | 10 V 0.1580 MHz conforming to IEC 61000-4-6 |
|---|---|
| Jistai Balloes | 3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL) 10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL) |
| Electromagnetic Emission | Conducted emissions - test level: 12069 dBµV/m QP (power lines) at 10150 kHz conforming to IEC 55011 |
| | Conducted emissions - test level: 63 dBµV/m QP (power lines) at 1.530 MHz |
| | conforming to IEC 55011 Radiated emissions - test level: 40 dBµV/m QP class A at 30230 MHz conforming |
| | to IEC 55011 Conducted emissions - test level: 7963 dBµV/m QP (power lines) at 1501500 |
| | kHz conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A at 230…1000 MHz |
| | conforming to IEC 55011 |
| mmunity To Microbreaks | 10 ms |
| Ambient Air Temperature For | -1050 °C (vertical installation) |
| Operation | -1055 °C (horizontal installation) |
| Ambient Air Temperature For Storage | -2570 °C |
| Relative Humidity | 1095 %, without condensation (in operation) |
| | 1095 %, without condensation (in storage) |
| p Degree Of Protection | IP20 with protective cover in place |
| Pollution Degree | 2 |
| Operating Altitude | 02000 m |
| Storage Altitude | 03000 m |
| /ibration Resistance | 3.5 mm at 58.4 Hz on symmetrical rail |
| | 3 gn at 8.4150 Hz on symmetrical rail 3.5 mm at 58.4 Hz on panel mounting |
| | 3 gn at 8.4150 Hz on panel mounting |
| Shock Resistance | 15 gn for 11 ms |
| Packing Units | |
| Jnit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12.8 cm |
| Package 1 Width | 11.45 cm |
| Package 1 Length | 18.6 cm |
| Package 1 Weight | 799.0 g |
| Jnit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 30 cm |

Package 2 Width

Package 2 Length

Package 2 Weight

30 cm

40 cm

9.588 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free | |
|----------|----------------------------|-----|
| | Rohs Exemption Information | Yes |
| ⊘ | Pvc Free | |

Certifications & Standards


| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |


Product datasheet

TM241C24U

Dimensions Drawings


Dimensions







Mounting and Clearance


Clearance






Mounting Position





TM241C24U


Acceptable Mounting



NOTE: Expansion modules must be mounted above the logic controller.

Incorrect Mounting








Direct Mounting On a Panel Surface


Mounting Hole Layout




Connections and Schema

Digital Inputs

Wiring Diagram





(*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally

(A): Sink wiring (positive logic)


(B): Source wiring (negative logic)

Fast Input Wiring (I0...I7)



Fast Transistor Outputs


Wiring Diagram



- (*): Type T fuse
- (1) The V0+, V1+, V2+ and V3+ terminals are not connected internally.
- (2) The V0-, V1-, V2- and V3- terminals are not connected internally.

Transistor Outputs

Wiring Diagram



(*): Type T fuse

(1): The V1+ and V2+ terminals are not connected internally.

(2): The V1- and V2- terminals are not connected internally.

USB Mini-B Connection

25-Apr-2024

