## **Product datasheet**

Specification





# Easy UPS 3S 20 kVA 400 V 3:1 UPS for external batteries

E3SUPS20K3I

## **Overview**

| Presentation | High-efficiency 3-phase UPS that features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 20 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is supplied without batteries, so you can easily customize the battery solution. |
|--------------|--|
| Lead Time    | Usually Ships within 6 Weeks   |

#### Main

| Main Input Voltage   | 400 V 3 phases     |  |
|----------------------|--------------------|--|
| Other Input Voltage  | 380 V              |  |
|                      | 415 V              |  |
| Main Output Voltage  | 230 V              |  |
| Other Output Voltage | 220 V              |  |
|                      | 240 V              |  |
| Rated Power In W     | 20 kW              |  |
| Rated Power In Va    | 20 kVA             |  |
| Provided Equipment   | Dust filter        |  |
|                      | Installation guide |  |

### **Batteries & Runtime**

| Efficiency                     | View Efficiency Graph ☐ |  |
|--------------------------------|-------------------------|--|
| Battery Type                   | External battery system |  |
| Maximum Short-Circuit Current  | 10 kA                   |  |
| Number Of Battery Filled Slots | 0                       |  |
| Number Of Battery Free Slots   | 0                       |  |

## **Physical**

| Colour         | White (RAL 9003) |
|----------------|------------------|
| Height         | 77 cm            |
| Width          | 25 cm            |
| Depth          | 80 cm            |
| Net Weight     | 58 kg            |
| Usb Compatible | Yes              |

## Input

| Maximum Input Current           | 37 A     |
|---------------------------------|----------|
|                                 |          |
| Input Power Factor At Full Load | 0.99     |
| Input Voltage Limits            | 304477 V |
| Network Frequency               | 4565 Hz  |

## Output

| Maximum Configurable Power In Va | 20 kVA                                     |  |
|----------------------------------|--|--|
| Maximum Configurable Power In W  | 20 kW                                      |  |
| Output Frequency                 | 50 Hz sync to mains<br>60 Hz sync to mains |  |
| Harmonic Distortion              | Less than 3 %                              |  |
| Output Overload Operation        | 10 minutes at 125% and 60 seconds at 150%  |  |
| Ups Type                         | Double conversion online                   |  |
| Crest Factor                     | 3:1  |  |

#### Conformance

| <b>Product Certifications</b> | CE  |  |
|-------------------------------|-----|--|
|                               | EAC |  |
|                               | RCM |  |

### **Environmental**

| Ambient Air Temperature For Operation | 040 °C               |
|---------------------------------------|----------------------|
| Relative Humidity                     | 095 % non-condensing |
| Operating Altitude                    | 03281 ft             |
| Ambient Air Temperature For Storage   | -1540 °C             |
| Storage Relative Humidity             | 095 % non-condensing |
| Storage Altitude                      | 0.0015240.00 m       |
| Acoustic Level                        | 60 dBA               |
| Heat Dissipation                      | 870 W                |
| Ip Degree Of Protection               | IP20                 |

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 101.5 cm |
| Package 1 Width              | 98.2 cm  |
| Package 1 Length             | 40 cm    |
| Package 1 Weight             | 75 kg    |

## **Contractual warranty**

Warranty 1 year on-site repair or replace with factory authorized Start-Up



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |  |
|--------------------------|---|--|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |  |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |  |
| Environmental Disclosure | Product Environmental Profile   |  |
| Circularity Profile      | End of Life Information   |  |