# **Product datasheet**

Specifications





# Galaxy VS UPS 100kW 400V for up to 5 internal 9Ah smart modular battery strings, Start-up 5x8

GVSUPS100K0B5HS

#### Overview

Presentation	Highly efficient, easy-to-deploy 100kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 5 smart modular high capacity battery strings, but is supplied without batteries, so you can easily customize the battery runtime. Includes 5x8 start-up service.
Lead Time	Usually Ships within 2 Weeks
Main	
Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated Power In W	100 kW
Rated Power In Va	100 kVA
Battery Type	Internal modular battery VRLA
Provided Equipment	Dust filter

## **Batteries & Runtime**

Efficiency	View Efficiency Graph ☐
Battery Voltage	480 V
Discharge Battery Voltage	384 V
Max Current Discharge	271 A
Battery Power In Vah	0 VAh runtime
Extended Runtime	0

Installation manual

Start-up service EcoStruxure Ready

Integrated network management

## **General**

Redundant No

## **Physical**

Colour White

Height	197 cm
Width	55 cm
Depth	84.7 cm
Net Weight	250 kg
Usb Compatible	No

# Input

Network Frequency	4070 Hz
Input Voltage Limits	340460 V 400 V
Maximum Input Current	180 A
Max Short Time Withstand Current	65 kA
Input Harmonic Distortion	Less than 3 % for full load
Load Power Factor	From 0.7 leading to 0.7 lagging without any derating
Input Power Factor At Full Load	0.99

# Output

<u> </u>	
Maximum Configurable Power In W	100 kW
Harmonic Distortion	Less than 3 %
Output Frequency	50 Hz sync to mains 60 Hz sync to mains
Crest Factor	2.5
Wave Type	Sine wave
Output Voltage Tolerance	+/- 5% after 2ms +/-1% after 50ms
Output Harmonic Distortion	< 1% linear load and < 3% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Bypass Type	Built-in static bypass
Maximum Configurable Power In Va	100 kVA

# Conformance

Standards	IEC 62040-1-1
	IEC 62040-2
	OSHPD

## **Environmental**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	03300 ft
Ambient Air Temperature For Storage	-1540 °C
Storage Relative Humidity	1080 % non-condensing
Storage Altitude	0.003048.00 m
Acoustic Level	65 dBA
Heat Dissipation	12377 Btu/h

## **Communications & Management**

Control Panel Touch screen LCD user interface

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	208.2 cm
Package 1 Width	101 cm
Package 1 Length	75.5 cm
Package 1 Weight	250 kg

## **Contractual warranty**

Warranty

<sup>1</sup> year on-site repair or replace with factory authorized Start-Up

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

#### Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Mercury Free

Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

China RohS declaration

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information

19-Apr-2024