



rotating mirror beacon XVR - Ø 165 - yellow - 25 W - 24 V AC DC

XVR1B08

! Discontinued on: 01-Nov-2020

(!) Discontinued

Main

| Range Of Product | Harmony XVR Application | |
|---------------------------|-------------------------------|--|
| Product Or Component Type | Rotating mirror beacon | |
| Component Name | XVR | |
| Mounting Diameter | 165 mm | |
| Light Source | Bulb included, yellow | |
| Bulb Type | Incandescent with BA 15d base | |
| Power Dissipation In W | 25 W | |
| [Us] Rated Supply Voltage | 24 V AC/DC | |

Complementary

| Material | Glass reinforced polyamide 6: base unit Polycarbonate: domed lens unit | |
|--|---|--|
| Clamping Connection Capacity | <= 1 x 1.5 mm² | |
| Cable Entry | 1 tapped entry for cable gland (included) for M20 | |
| [Ui] Rated Insulation Voltage | 250 V conforming to EN/IEC 60947-1 | |
| Current Consumption | onsumption < 1050 mA | |
| [Uimp] Rated Impulse Withstand Voltage | npulse Withstand 4 kV conforming to EN/IEC 60947-1 | |
| Service Life In Hours | 2000 h | |
| Operating Position | Horizontal | |
| Flashing Frequency | 3 Hz | |
| Cad Overall Width | 165 mm | |
| Cad Overall Height | leight 202 mm | |
| Cad Overall Depth | 165 mm | |
| Net Weight | 1.165 kg | |

Environment

20-Apr-2024

| Standards | EN/IEC 60947-5-1 |
|-------------------------------------|---------------------------|
| | EN/IEC 60947-1 |
| | CSA C22.2 No 14 UL 508 |
| | UL 300 |
| Protective Treatment | тс |
| Ambient Air Temperature For Storage | -4070 °C |

| Ambient Air Temperature For Operation | -2050 °C |
|---------------------------------------|--|
| Electrical Shock Protection Class | Class I conforming to EN/IEC 61140 |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Nema Degree Of Protection | NEMA 4X conforming to UL 508 (indoor) NEMA 4X conforming to CSA C22 (indoor) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Toxic Heavy Metal Free | |
|----------|----------------------------|-----|
| | Mercury Free | |
| ② | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |