Product datasheet

Specification





TeSys F contactor - 4P (4 NO) - AC-1 - <= 440 V 200 A - coil 48 V AC

LC1F1154E7

Discontinued on: 10-Oct-2020

! End-of-service on: 04-Nov-2020

① Discontinued

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	48 V AC 40400 Hz
[le] Rated Operational Current	200 A (at <40 °C) at <= 440 V AC-1

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 40 °C)
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand	1100 A 40 °C - 10 s
Current	640 A 40 °C - 30 s
	520 A 40 °C - 1 min
	400 A 40 °C - 3 min
	320 A 40 °C - 10 min
Associated Fuse Rating	125 A aM at <= 440 V
	200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1
	1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	4 NO
Control Circuit Voltage Limits	Operational: 0.851.1 Uc 40400 Hz (at 55 °C)
	Drop-out: 0.20.55 Uc 40400 Hz (at 55 °C)
Mechanical Durability	10 Mcycles
Inrush Power In Va	770 VA, 40400 Hz cos phi 0.9 (at 20 °C)

23-Apr-2024 Life Is On Schneider



Hold-In Power Consumption In Va	8.1 VA, 40400 Hz cos phi 0.9 (at 20 °C)
Maximum Operating Rate	2400 cyc/h 55 °C
Operating Time	35 ms closing (at Uc) 130 ms opening (at Uc)
Connections - Terminals	Power circuit: bar 2 cable(s) - busbar cross section: 20 x 3 mm Power circuit: lugs-ring terminals 1 cable(s) 95 mm² Power circuit: connector 1 cable(s) 95 mm² Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 125 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid without cable end Power circuit: bolted connection
Tightening Torque	Power circuit: 10 N.m Control circuit: 1.2 N.m
Mounting Support	Plate
Heat Dissipation	5.97.2 W
Standards	IEC 60947-4-1 EN 60947-1 JIS C8201-4-1 EN 60947-4-1 IEC 60947-1
Product Certifications	CB CCC UL ABS BV RMRoS RINA DNV LROS (Lloyds register of shipping)
Compatibility Code	LC1F
Control Circuit Type	AC at 40400 Hz
Environment	
Ip Degree Of Protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Protective Treatment	тн
Ambient Air Temperature For Operation	-4060 °C
Ambient Air Temperature For Storage	-6080 °C
Permissible Ambient Air Temperature Around The Device	6070 °C at Uc
Height	162 mm
Width	200.5 mm
Depth	171 mm
Operating Altitude	3000 m without derating
Net Weight	3.83 kg
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22 cm

21.5 cm

Package 1 Width

Package 1 Length	26.5 cm
Package 1 Weight	4.82 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information