Product datasheet

Specifications





10AX 250V 1 Gang Intermediate Switch, White

A3G31B3A_WE_G11

Main

Range	Affle Plus	
Product Or Component Type	Switch	
Device Application	Control switch	
Load Type	Fluorescent lamp Inductive Resistive Incandescent lamp	
Colour Tint	White	

Complementary

Device Mounting	Flush	
Switch Function	Intermediate	
Cable Cross Section	4 mm² stranded cable	
	2.5 mm² solid cable	
	2.5 mm² stranded cable	
	4 x 4 mm² solid cable for AC	
Rated Current	10 AX at 250 V AC	
Number Of Gangs	1 gang	
Material	Polycarbonate: grid plate	
	Polycarbonate: base	
	Polycarbonate: dolly	
	Polycarbonate: surround	
	Polycarbonate: actuator	
Connections - Terminals	Screw terminal	
Embedding Depth	24.9 mm	
Width	86 mm	
Height	86 mm	
Depth	35.6 mm	

Environment

Maximum Ambient Air Temperature For Operation	35 °C
Relative Humidity	095 %
Operating Altitude	5000 m
Product Certifications	IEC
Standards	BS EN 60669-1 MS IEC 60669-1 IEC 60669-1

8 May 2024 Life Is On Schneider

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	83 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	670 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	96
Package 3 Height	21 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	8.54 kg

8 May 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations