

Product datasheet

Specifications



10AX 250V 3 Gang 2 Way Switch, White

A3G33B2A_WE_G11

Main

Range	Affle Plus
Product Or Component Type	Switch
Device Application	Control switch
Load Type	Incandescent lamp Resistive Inductive Fluorescent lamp
Colour Tint	White

Complementary

Device Mounting	Flush
Switch Function	2-way
Cable Cross Section	4 mm ² stranded cable 2.5 mm ² solid cable 2.5 mm ² stranded cable 9 x 4 mm ² solid cable for AC
Rated Current	10 AX at 250 V AC
Number Of Gangs	3 gangs
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: surround Polycarbonate: actuator
Connections - Terminals	Screw terminal Brass terminal
Embedding Depth	24.9 mm
Width	86 mm
Height	86 mm
Depth	35.6 mm

Environment

Maximum Ambient Air Temperature For Operation	35 °C
Relative Humidity	0...95 %
Operating Altitude	5000 m
Product Certifications	IEC
Standards	IEC 60669-1 MS IEC 60669-1 BS EN 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	96 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	768 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	96
Package 3 Height	21 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	9.716 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations