Product datasheet





NEO 250V 10A 1Gang 2way Switch with White

E3031H2_EWWW_G11

- ! Discontinued on: 30 Jun 2023
- ! End-of-service on: 2 Jan 2024

① Discontinued

Main

Range	Neo
Product Or Component Type	Control switch
Device Application	Control
Wiring Device Mounting	Flush Surface
Switch Function	2-way
Switch Application	Switch
Load Type	Inductive Incandescent lamp Fluorescent lamp Resistive
Bulb Type	LED (white)
Colour Tint	White

Complementary

Rated Current	10 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part
	Steel: metal parts
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s)
	3 x 2.5 mm ² for stranded cable(s)
	4 x 1.5 mm² for solid cable(s)
	4 x 1.5 mm² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use

Life Is On Schneider 23 Apr 2024

Standards EN 60669-1
GB 16915.1
IEC 60669-1

Packing Units

PCE
1
3.6 cm
8.7 cm
8.7 cm
68 g
BB1
8
15 cm
19 cm
8 cm
558 g
CAR
80
21 cm
31 cm
50 cm
6580 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations