

Product datasheet

Specifications



Complete joystick controller, Harmony XK, XKBA light hoisting applications

XKBA1133CA

⚠ Discontinued on: 31 Oct 2022

⚠ Discontinued

Main

| | |
|------------------------------|------------------------------|
| Range Of Product | Harmony XK |
| Product Or Component Type | Complete joystick controller |
| Product Specific Application | Light hoisting applications |

Complementary

| | |
|---------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device Short Name | XKB |
| Bezel Material | Metal |
| Fixing Collar Material | Metal |
| Sale Per Indivisible Quantity | 1 |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -40...70 °C |
| Ambient Air Temperature For Operation | -20...70 °C |
| Overvoltage Category | Class I conforming to IEC 61140 |
| Standards | CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1 |
| Operator Position Information | All positions |
| Operator Profile | Standard handle |
| Notch Per Direction | 1...3 notches at 0-12°-20°-28° for each direction |
| Mechanical Durability | 1000000 cycles |
| Vibration Resistance | 6 gn (f= 1...70 Hz) conforming to IEC 60068-2-6 |
| Shock Resistance | 20 gn (duration = 11 ms) conforming to IEC 60068-2-27 |
| Connections - Terminals | Captive screw clamp terminals, <= 2 x 1.5 mm² with cable end Captive screw clamp terminals, <= 1 x 2.5 mm² without cable end Captive screw clamp terminals, >= 1 x 0.5 mm² |
| Short-Circuit Protection | 10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1 |
| [Ith] Conventional Free Air Thermal Current | 10 A conforming to EN/IEC 60947-5-1 10 A conforming to CSA C22.2 No 14 10 A conforming to UL 508 |
| [Ui] Rated Insulation Voltage | 500 V (pollution degree 3) conforming to IEC 60947-1 |
| Compatibility Code | XKB |

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 24.2 cm |
| Package 1 Width | 16.4 cm |
| Package 1 Length | 15.2 cm |
| Package 1 Weight | 1.03 kg |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 30 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 2.642 kg |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 16 |
| Package 3 Height | 77 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 60 cm |
| Package 3 Weight | 30.78 kg |

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--------------------------------------------------------------------------------------------------------------|------------------------------------------------------------|
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |