

# Product datasheet

Specifications



## Acti9 - IHP + - digital time switch - 24 hours + 7 days - 3 years memory

15837

⚠ Discontinued on: 23 Jan 2021

⚠ Discontinued

### Main

Range Of Product	Acti9
Product Name	Acti9 IHP
Device Short Name	IHP
Product Or Component Type	Programmable digital time switch
Device Application	Building
Battery Type	Lithium
Number Of Channels	1
Language	Dutch Finnish French Danish English Norwegian Swedish
Colour Tint	White (RAL 9003)

### Complementary

Product Compatibility	Mechanical compatibility with electrical distribution comb busbars
Power Consumption In Va	3 VA
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50/60 Hz
Number Of Inputs	1 input(s) impulse and maintained
Accuracy	+/- 1 s/day 20 °C
Cycle Duration	24 hours + 7 days
Maximum Number Of Switchings	42
Minimum Interval Duration	1 min
Function Available	Automatic winter/summer time changeover Pulse programming
Display Type	Backlit LCD
Battery Life	5 year(s)
Backup Time	3 years time and program saving
Type Of Setting	Random function Absence for holidays function
Connections - Terminals	screw terminals

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Support	DIN rail
9 Mm Pitches	2
Width	18 mm
Height	85 mm
Depth	66 mm
Net Weight	0.09 kg
Function	Pulse programming and random function
Absence For Holidays	Yes
Time Changeover	Automatic
Updated By	None
Compatibility Code	IHP

## Environment

Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	IP20 B

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	3 cm
Package 1 Length	11 cm
Package 1 Weight	0.131 kg

## Contractual warranty

Warranty	18 months
----------	-----------