

Product datasheet

Specifications



Vivace 20A 250V 1Gang 2W DP Switch withN&E,Aluminium silver

KB31D20NE_2_AS_G2

Main

Range	Vivace
Product Or Component Type	Switch
Device Short Name	KB31
Device Application	Control
Switch Function	2-way

Complementary

Device Presentation	Complete mechanism
Actuator	Rocker
Pilot Light	Neon indicator lamp
Number Of Gangs	1 gang
Colour Tint	Aluminium silver
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	35 mm
Rated Current	20 A at 250 V AC, inductive 20 A at 250 V AC, resistive
[Ue] Rated Operational Voltage	250 V AC
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	pillar terminal
Terminal Identifier	L2 N2 L1 N1
Tightening Torque	0.4 N.m
Clamping Connection Capacity	<= 2.5 mm²
Width	86 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	86 mm
--------	-------

Environment

Standards	SS 227 IEC 60669-1 MS IEC 60669-1
Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1