# **Product datasheet**

Specifications





# Easy TeSys differential thermal overload relay 23...32 A - class 10A

LRE353

#### Main

Range	Easy TeSys
Range Of Product	Easy TeSys Protect
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRE
Relay Application	Motor protection
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0 conforming to IEC 60947-4-1

# Complementary

· · · · · · · · · · · · · · · · · ·	
Product Compatibility	LC1E4095
Network Type	AC
Network Frequency	5060 Hz
Mounting Support	Under contactor Plate, with specific accessories Rail, with specific accessories
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1
Signalling Function	Relay trip indicator
Thermal Protection Adjustment Range	2332 A
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1
Mechanical Robustness	Shocks: 6 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 GN conforming to IEC 60068-2-6
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
[Ue] Rated Operational Voltage	<= 690 V AC
Associated Fuse Rating	63 A gG for power circuit 40 A aM for power circuit 5 A gG for signalling circuit
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV
Local Signalling	Trip indicator
Control Type	Push-button red stop: Push-button green reset:
Temperature Compensation	-2060 °C

Connections - Terminals Signalling circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: without cable end   Signalling circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: cable end   Signalling circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: cable end   Power circuit: screw clamp terminals 1 435 mm² - cable stiffness: flexic cable end	flexible with solid without
cable end Signalling circuit: screw clamp terminals 2 1…2.5 mm² - cable stiffness: cable end Power circuit: screw clamp terminals 1 4…35 mm² - cable stiffness: flexi	solid without
cable end Power circuit: screw clamp terminals 1 435 mm² - cable stiffness: flexi	
	ible without
	Power circuit: screw clamp terminals 1 435 mm <sup>2</sup> - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 435 mm <sup>2</sup> - cable stiffness: flexible with cable end
•	
Power circuit: screw clamp terminals 1 435 mm <sup>2</sup> - cable stiffness: solic cable end	d without
Recommended Tightening Torque Power circuit: 9 N.m - on screw clamp terminals Signalling circuit: 1.7 N.m - on screw clamp terminals	
Height 54 mm	
Width 70 mm	
Depth 113 mm	
Net Weight 0.47 kg	

#### Environment

Standards	IEC 60947-5-1 IEC 60947-4-1
Product Certifications	EAC
Protective Treatment	TH conforming to IEC 60068
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-2060 °C without derating conforming to IEC 60947-4-1 -2070 °C with derating
Ambient Air Temperature For Storage	-6080 °C
Fire Resistance	850 °C conforming to IEC 60068-2-1
Dielectric Strength	6 kV at 50 Hz conforming to IEC 60255-5
Electromagnetic Compatibility	Surge withstand: 6 kV conforming to IEC 60801-5

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	9 cm
Package 1 Length	12.5 cm
Package 1 Weight	490 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.787 kg

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information