



Circuit breaker, ComPact NSX100B, 25kA/415VAC, TMD trip unit 40A, 3 poles 2d

LV429544

! Discontinued on: 31-Dec-2020

! End-of-service on: 12-Mar-2024

① Discontinued

Main

- Iviairi	
Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100250
Device Short Name	NSX100B
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	3P
Protected Poles Description	2t
[In] Rated Current	40 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	15 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	B 25 kA 415 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	Ц
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ics] Rated Service Short-Circuit Breaking Capacity	20 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 7.5 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2

Mechanical Durability	50000 cycles
Electrical Durability	10000 cycles at 690 V In 20000 cycles at 690 V In/2 30000 cycles at 440 V In 50000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rating	40 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.71 x ln
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	120400 s at 1.5 x ln 15 s at 6 x lr
Short-Time Protection Pick-Up Adjustment Type Isd	Fixed
[Isd] Short-Time Protection Pick- Up Adjustment Range	500 A
Short-Time Protection Delay Adjustment Type Tsd	Fixed
Earth-Leakage Protection	Without
Number Of Slots For Electrical Auxiliaries	5 slot(s)
Width (W)	105 mm
Height (H)	161 mm
Depth (D)	86 mm
Net Weight	2.05 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins