Product datasheet

Specifications





module XPSAC, Emergency stop, 24 VAC and VDC

XPSAC5121

Price: 214,593.75 NGN

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAC
Safety Module Application	For emergency stop and switch monitoring
Function Of Module	Emergency stop Switch monitoring
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061
Safety Reliability Data	MTTFd = 210.4 years conforming to EN/ISO 13849-1 DC > 99 % conforming to EN/ISO 13849-1 PFHd = 3.56E-9 1/h conforming to EN/IEC 62061
Type Of Start	Unmonitored
Connections - Terminals	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm ² flexible without cable end Captive screw clamp terminals, 1 x 0.141 x 2.5 mm ² solid without cable end Captive screw clamp terminals, 1 x 0.251 x 1.5 mm ² flexible with cable end, with bezel Captive screw clamp terminals, 1 x 0.251 x 2.5 mm ² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.142 x 0.75 mm ² flexible without cable end Captive screw clamp terminals, 2 x 0.142 x 0.75 mm ² flexible without cable end Captive screw clamp terminals, 2 x 0.142 x 0.75 mm ² solid without cable end Captive screw clamp terminals, 2 x 0.252 x 1 mm ² flexible with cable end, without bezel
Output Type	Relay instantaneous opening, 3 NO circuit(s), volt-free
Number Of Additional Circuits	1 solid state output
[Us] Rated Supply Voltage	24 V AC - 2010 % 24 V DC - 2020 %

Complementary

· · ·	
Supply Frequency	50/60 Hz
Maximum Power Consumption In W	1.2 W DC
Maximum Power Consumption In Va	2.5 VA AC
[Uc] Control Circuit Voltage	24 V
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Output Thermal Current	6 A per relay for relay output
[Ith] Conventional Free Air Thermal Current	10.5 A

4 A gG or gL for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200	
10 mA for relay output	
16 V for relay output	
100 ms	
300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1	
4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1	
2 LEDs	
40 mA at 24 V DC on power supply 90 mA at 24 V AC on power supply	
35 mm symmetrical DIN rail	
0.16 kg	

Environment

Standards	EN/IEC 60947-5-1 EN/ISO 13850 EN 60204-1 EN 1088/ISO 14119
Product Certifications	UL CSA TÜV
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For Storage	-2585 °C

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	10.400 cm
Package 1 Length	12.000 cm
Package 1 Weight	196.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	16
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.478 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	512
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm

Package 3 Length	80.000 cm	
Package 3 Weight	115.540 kg	

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information