


Produktdatablad

Spesifikasjoner



Lystrykknapphode i metall for LED med riflet linse, fjærretur og opphøyd trykflate i rød farge

ZB4BW143S

! Utgått: 28. okt. 2020

! Utgått

EAN: 3389110174274

Teknisk informasjon

Produktspekter	Harmony XB4
Produkt Eller Type Komponent	Hode for lystrykknapper
Kortnavn Utstyr	ZB4
Produktkompatibilitet	Innebygget LED
Innfatningsmateriale	Forkrommet metall
Hode Type	Standard
Montasjediameter	22 mm
Salg Per Udelelig Kvantitet	1
Formen På Varslingsenhetens Hode	Rund
Type Arm/Stempel	fjærretur
Operatørprofil	Rød opphøyd, umerket
Knappens Tilleggs Info.	Med rillet deksel
Miljøegenskaper	Miljø med mye belysning

Komplementær

Bredde	29 mm
Høyde	29 mm
Dybde	33 mm
Vekt	0,026 kg
Resistens Til Høytrykksvask	7000000 Pa på 55 °C, distanse : 0.1 m
Mekanisk Levetid	10000000 sykkluser
Elektrisk Sammensetningskode	M1 for <6 kontakter bruker Enkel blokker i frontmontering med innebygget LED M2 for <6 kontakter bruker enkel og dobbel blokker i frontmontering med innebygget LED M6 for <2 kontakter bruker Enkel blokker i frontmontering med integrert LED og transformator M10 for <2 kontakter bruker Enkel blokker i frontmontering med innebygget LED
Enhetens Utseende	Basic sub-assemblies

Miljø

Overflatebeskyttelse	TH
Omgivelsestemperatur For Lagring	-40...70 °C
Omgivelsestemperatur Drift	-40...70 °C

Ansvarsfriskivelse: Dokumentasjonen erstatter ikke opplysninger om produktene, og skal ikke brukes til å fastslå produktenes egnethet eller driftssikkerhet for bestemte bruksområder.

Overspenningskategori	Klasse I i samsvar med IEC 60536
Ip-Grad	IP66 i samsvar med IEC 60529 IP69 IP69K
Nema Beskyttelsesgrad	NEMA 13 NEMA 4X
Ik Beskyttelsesklasse	IK05 conforming to EN 50102
Standarder	EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C8201-5-1 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-5 UL 508 JIS C8201-1
Produktsertifikater	BV GL UL listet DNV CSA LROS (Lloyds register of shipping)
Vibrasjonsmotstand	5 gn (f= 2...500 Hz) i samsvar med IEC 60068-2-6
Støtmotstand	30 gn (varighet = 18 ms) for halvsinuskurve akselerasjon i samsvar med IEC 60068-2-27 50 gn (varighet = 11 ms) for halvsinuskurve akselerasjon i samsvar med IEC 60068-2-27

Garantiperiode

Garanti	18 months
---------	-----------



Green Premium™-merket er Schneider Electrics forpliktelse til å levere produkter med den beste miljøytelsen i sin klasse. Green Premium lover samsvar med de nyeste forskriftene, åpenhet om miljøpåvirkning samt sirkulære og lite CO₂-produkter.

Veiledning til vurdering av produktets bærekraft er en innsiktsrapport som klargjør globale miljømerkestandarder og hvordan du tolker miljøerklæringer.

[Les mer om Green Premium >](#)

[Veiledning i vurdering av bærekraften til et produkt >](#)



Transparens RoHS/REACH

Tilfredshetsresultater


✓	Reach Fri For Svhc	
✓	Fri For Giftige Tungmetaller	
✓	Kvikksølvfri	
✓	Informasjon Om Rohs-Unntak	Ja

Sertifiseringer og standarder

Reach-Regelverk	REACH-erklæring
Eu Rohs-Direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet) EU RoHS-erklæring
Kinas Rohs-Forskrift	Kinas RoHS-erklæring
Miljøinformasjon	Produktmiljøprofil
Produktets Livssyklus	Informasjon om levetidsslutt

Dimensions Drawings

Dimensions




Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board	Connection by Faston Connectors
(1) Diameter on finished panel or support (2) 40 mm min. / 1.57 in. min. (3) 30 mm min. / 1.18 in. min. (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm^{+0.4}₀ / 0.88 in.^{+0.016}₀) (5) 45 mm min. / 1.78 in. min. (6) 32 mm min. / 1.26 in. min.	

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Panel Cut-outs (Viewed from Installer’s Side)




A: 30 mm min. / 1.18 in. min.

B: 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)


Dimensions in mm



A: 30 mm min.

B: 40 mm min.

Dimensions in in.



A: 1.18 in. min.
B: 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in: T1 + T2 = 0.3 mm max.

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm $\pm$ 0.1 / 0.88 in. $\pm$ 0.004
- Orientation of body/fixing collar ZB4 BZ009: $\pm 2^{\circ} 30'$ (excluding cut-outs marked a and b).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
 - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
 - with each selector switch head (ZB4 BD•, ZB4 BJ•, ZB4 BG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Panel
(2) Printed circuit board


Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$ for centring adapter ZBZ 01•
- 3 $8 \times \varnothing 1.2 \text{ mm} / 0.05 \text{ in.}$ holes
- 4 1 hole $\varnothing 2.9 \text{ mm} \pm 0.05 / 0.11 \text{ in.} \pm 0.002$, for aligning the printed circuit board (with cut-out marked **a**)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked **b**)
- 6 4 holes $\varnothing 2.4 \text{ mm} / 0.09 \text{ in.}$ for clipping in adapter ZBZ 01•

Dimensions An + 18.1 relate to the $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$ holes for centring adapter ZBZ 01•.

Technical Description


Electrical Composition Corresponding to Codes M1 and M7




Electrical Composition Corresponding to Codes M2 and M8



Electrical Composition Corresponding to Codes M6 and P2



Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2



Legend

Single contact



Double contact



Light block



Possible location

