



Main

Range	Linergy
Range of product	Linergy
Product or component type	Busbar
Product name	Linergy BW
Range compatibility	Prisma G enclosure Prisma P enclosure
IP degree of protection	IPxx B
Busbar description	Insulated bar
Provided equipment	Clip-on covers
Quantity per set	Set of 1

Complementary

Poles description	4P
Installation direction	Vertical, operating position: rear
Installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	125 A
[Icw] rated short-time withstand current	8.5 kA (1 s)
[Ipk] rated peak withstand current	20 kA
I ² t on activation	72250 kA ² .s
Permissible current	125 A
Length	750 mm

Net weight	2.34 kg
Type of busbar connection	M6 threaded hole
Connection pitch	Connection each 25 mm

Environment

Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.4 kg
Package 1 Height	3.5 cm
Package 1 width	11.5 cm
Package 1 Length	91 cm
Unit Type of Package 2	P12
Number of Units in Package 2	120
Package 2 Weight	280.8 kg
Package 2 Height	80 cm
Package 2 width	80 cm
Package 2 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product