



## LINERGY FC DISTRIBUTION BLOCK FOR COMPACT NSX250 3P FIXED W/O CONNECTION

04407

! Discontinued on: 23/03/2023

① Discontinued

#### Main

Range	Linergy
	<del></del>
Range Of Product	Linergy
Product Or Component Type	Device feeder
Product Name	Linergy FC
Accessory / Separate Part Category	Connection accessory
Range Compatibility	Prisma Prisma P cubicle

### Complementary

Installation Description	Cubicle - width 650 mm
Number Of Devices	4 (3P)
Polos Description	20

Installer	d Device
mstaned	a Device

ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation

ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation

ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation

ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation

ComPact: fixed INS250 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: fixed NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation

ComPact: fixed NSX250 without earth leakage protection - control: motor mechanism - vertical installation

ComPact: plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: plug-in NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: plug-in NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation

ComPact: plug-in NSX250 without earth leakage protection - control: motor mechanism - vertical installation

 ${\tt ComPact: plug-in \, NSX100...160 \, without \, earth \, leakage \, protection \, -control: \, toggle \, -vertical \, installation}$ 

ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation

ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: fixed NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation

ComPact: fixed NSX250 with earth leakage protection - control: motor mechanism - vertical installation

ComPact: plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: plug-in NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: plug-in NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation

ComPact: plug-in NSX250 with earth leakage protection - control: motor mechanism - vertical installation

ComPact: plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation

ComPact: plug-in NSX250 with earth leakage protection - control: toggle - vertical installation

Mounting Support	Mounting plate
Installation Direction	Horizontal
[Ui] Rated Insulation Voltage	750 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[le] Rated Operational Current	800 A at 40 °C
[Ue] Rated Operational Voltage	690 V
[lpk] Rated Peak Withstand Current	50 kA
I <sup>2</sup> T On Activation	25000000 A².s
Permissible Current	800 A at 40 °C 725 A at 60 °C 675 A at 70 °C
Connections - Terminals	Outgoer: plug in (phase) , 4 outgoers
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA KEMA

Quantity Per Set	Set of 1
Length	440 mm
Height	132 mm
Depth	235 mm
Net Weight	6 kg
Colour	Black

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information