

# Product datasheet

Specifications



## Minera Ground Mounted Oil Immersed Transformer 1000 kVA\_11kV\_OC\_BBBB\_CORR\_L2

MIN100011559700000

⚠ Discontinued on: 19-Jan-2022

⚠ End-of-service on: 03-Jun-2022

⚠ Discontinued

### Main

Product Range	Minera
Product Or Component Type	Oil type transformer
Dielectric Liquid	Mineral oil
Network Type	AC
Standards	IS 1180
Type Of Installation	Indoor/outdoor
Maximum Altitude	< 1000 m
Cooling Mode	ONAN (oil natural air natural)
Winding Material	Copper
Degree Of Protection	IP00 corrugated IS 2099 IP00 corrugated IS 3347
Mounting Mode	Ground mounted

### Complementary

Directives	2015/2014/548/EC- ecodesign
Phase	3 phases
Rated Power	1000 kVA
Rated Frequency	50 Hz
Rated Primary Voltage	11 kV
Secondary Voltage ( At No-Load)	Operation/loading as per IS standard: 433 V
Insulation Voltage To Industrial Frequency ( 50 Hz 1 Mn)	28 kV primary 3 kV secondary
Rated Insulation Level	Primary circuit: 12 kV Secondary circuit: 1.1 kV
Lighting Impulse Whistand Voltage ( Bil) , 1.2/50 Ms	75 kV
Vector Group	Dyn11
Hv Tappings (Off Circuit)	- 10...5 x 2.5 %
Short Circuit Impedance	5 %
Temperature Rise Of Windings	(winding) 60 K (winding)
Thermal Class	A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Connection	Bare bushing high voltage connection Bare bushing low voltage connection
Protective Relay	DMCR relay
Locking Options Description	Without keylocks
Height	1800 mm
Width	1130 mm
Length	1550 mm
Total Weight	3360 kg

## Environment

Maximum Ambient Temperature	50 °C
Ambient Air Temperature For Operation	-6...50 °C
Ambient Air Temperature For Storage	-6...50 °C
Environmental Certification	0...95 %
Fire Certificate	Level 2

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	180 cm
Package 1 Width	113 cm
Package 1 Length	155 cm
Package 1 Weight	3360 kg

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information	