Product datasheet

Specifications





Power Factor controller - VarPlus Logic - VPL 6

VPL06N

Main

Range	PowerLogic
Product Name	PowerLogic PFC Controller
Device Short Name	VPL6
Product Or Component Type	Power factor controller

Complementary

Number Of Step Output Contacts	6
[Us] Rated Supply Voltage	90550 V AC <= 999 kV AC with external VT
Measurement Current	05 A
Measurement Voltage	90550 V AC 50/60 Hz
Operating Mode	Manual or automatic
Number Of Quadrant Operation For Generator Application	4
Device Connection	Communication protocol: Modbus interface: RS485
Input Function	Switch: 1 x dry contact
Colour Code	Front: dark grey RAL 7016
Display Type	Backlit LCD
Display Size	56 x 25 mm
Function Available	Automatic detection Advanced programming (expert) Manual programming Any step sequence Automatic initialisation
Metering Type	Power factor and displacement PF (signed, four quadrant) Total current harmonic distortion THD (I) Power factor average over lifetime Temperature maximum Phase current I1, I2, I3 RMS on load Active power P, P1, P2, P3 on load Reactive power Q, Q1, Q2, Q3 on load Apparent power S, S1, S2, S3 on load Voltage U21, U32, U13, V1, V2, V3 on load
Type Of Measurement	Ambient temperature inside the cubicle Tan ϕ Individual voltage harmonic

individual voltage harmonic

Cos φ Operating time Power factor

Capacitor current overload Irms/I1

Information Displayed	Number of switching cycles por stop
illiormation bisplayed	Number of switching cycles per step Remaining step capacity in %
	Individual step size in kVAr
Type Of Alarms	Step power loss (< 75 %) / Action: message and alarm contact + step blocked
•• • • • • • • • • • • • • • • • • • •	Step faulty / Action: message and alarm contact + step blocked
	High current (> 6 A CT) / Action: message and alarm contact
	Hunting (unstable regulation) / Action: message and alarm contact + step blocked
	Low current (< 15 mA CT) / Action: message and alarm contact
	Overcompensation / Action: message and alarm contact
	Capacitor current overload (Irms/I1) (> 130 % I1) / Action: message and alarm
	contact + step switched off
	Overtemperature (50 °C) / Action: message and alarm contact + step switched off
	Overtemperature (30 °C) / Action: fan switch
	Overvoltage (+/- 10 %) / Action: message and alarm contact + control stopped Total harmonic distortion (> 7 %) / Action: message and alarm contact + step
	switched off
Data Recording	5 alarms
Operational Hours Alarm	100000 h without maintenance
Operational Counter Alarm	65000 cycles without maintenance
 Input Type	Insensitive to phase rotation polarity
1 1 1 1 3 1 1 1	Insensitive to CT polarity
	Phase to neutral
	Current input CTX/5 A and X/1 A
	Phase to phase
Output Type	Control relay: 0.2 A 110 V DC
	Control relay: 1 A 48 V DC
	Control relay: 2 A 400 V AC 50/60 Hz
	Control relay: 1 A 24 V DC
	Control relay: 5 A 250 V AC 50/60 Hz
	Control relay: 5 A 120 V AC 50/60 Hz
	Fan: 5 A 250 V AC 50/60 Hz
	Fan: 1 A 48 V DC
	Alarm relay: 5 A 250 V AC 50/60 Hz
	Alarm relay: 1 A 48 V DC
Maximum At The Common Terminal	10 A
Settings Operating Mode	Manual
	Automatic
Type Of Setting	Choice of stepping programs: auto
	Choice of stepping programs: LIFO
	Choice of stepping programs: linear
	Delay between 2 successive switch on the same step: 51200 s
	Step configuration programming: auto
	Step configuration programming: off
	Step configuration programming: fixed
	Target cos phi: 0.7 inductive0.7 capacitive
	Target cos phi: dual cos φ
Measurement Accuracy	Voltage +/- 1 %
model of the transfer of the t	Current +/- 1 %
	Frequency +/- 1 %
	Energy (P,Q,S) +/- 2 %
	Cos φ +/- 2 %
	Total voltage harmonic distortion THD (U) +/- 2 %
	Individual voltage harmonic +/- 3 %
	Temperature +/- 3 °C
Time Delay Range	16500 s (on reconnection)
	16500 s (on response)
Provided Equipment	User manual
Mounting Mode	Flush-mounted
Mounting Support	Panel - thickness: 13 mm
Mounting Location	In cabinet
Cut-Out Dimensions	138 x 138 mm
Height	144 mm

Width	144 mm
Depth	58 mm
Net Weight	0.6 kg

Environment

Standards	IEC 61000-6-2 EN 61010-1 IEC 61000-6-4 IEC 61326-1 UL 61010-1
Product Certifications	EAC NRTL cNRTL CE
Ip Degree Of Protection	Front face: IP41 Rear face: IP20
Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	17.800 cm
Package 1 Length	18.400 cm
Package 1 Weight	696.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.050 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	64
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	60.348 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins