Product datasheet

Specification





round pilot light \emptyset 22 - orange - integral LED - 110 V AC - screw clamp terminal

XA2EVF5LC

Main

Range Of Product	Easy Harmony XA2	
Product Or Component Type	Monolithic pilot light	
Device Short Name	XA2	
Mounting Diameter	22.5 mm	
Shape Of Signaling Unit Head	Round	
Cap/Operator Or Lens Colour	Amber	
Light Source	LED	
Bulb Base	Integral LED	
[Us] Rated Supply Voltage	110 V AC/DC 50/60 Hz	

Complementary

o o pro o car y	
Terminals Description Iso N°1	(X1-X2)PL
Device Mounting	Fixing hole 22.3 +0.4/0 conforming to IEC 60947-5-1
Fixing Center	>= 30 x 40 mm (support panel) metal - thickness: 16 mm >= 30 x 40 mm (support panel) plastic - thickness: 26 mm
Fixing Mode	Fixing nut beneath head recommended torque: 2.2 N.m (+/- 0.2 N.m)
Marking	CCC CE
[Us] Rated Supply Voltage	110 V
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, 1 x 0.51 x 2.5 mm² without cable end conforming to IEC 60947-1
Tightening Torque	0.81 N.m conforming to IEC 60947-1
Shape Of Screw Head	Cross compatible with Philips No 2 screwdriver Slotted compatible with flat Ø 4 mm screwdriver Slotted compatible with flat Ø 5.5 mm screwdriver
[Ui] Rated Insulation Voltage	400 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1
Signalling Type	Steady
Supply Voltage Limits	0.81.2 V AC/DC
Current Consumption	<= 20 mA
Service Life	40000 h at rated voltage and 25 °C
Height	29 mm
Width	29 mm

Depth	53 mm
Net Weight	0.02 kg

Environment

Ambient Air Temperature For Storage	-4070 °C	
Ambient Air Temperature For Operation	-2570 °C	
Overvoltage Category	Class I conforming to IEC 536	
Ip Degree Of Protection	e Of Protection IP65 conforming to IEC 60529	
Ik Degree Of Protection	on IK05	
Standards	GB 14048.1 GB 14048.5 IEC 60947-1 IEC 60947-5-1 IEC 60529 IEC 50102	
Product Certifications	CE CCC	
Vibration Resistance	Resistance 5 gn (f= 12500 Hz) conforming to IEC 60068-2-6	
Shock Resistance 30 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27		

Packing Units

•		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.700 cm	
Package 1 Width	2.700 cm	
Package 1 Length	5.100 cm	
Package 1 Weight	21.000 g	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	10	
Package 2 Height	6.500 cm	
Package 2 Width	6.500 cm	
Package 2 Length	16.000 cm	
Package 2 Weight	236.000 g	
Unit Type Of Package 3	S02	
Number Of Units In Package 3	160	
Package 3 Height	15.000 cm	
Package 3 Width	30.000 cm	
Package 3 Length	40.000 cm	
Package 3 Weight	4.036 kg	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



e: Calmping thickness:1 to 6 mm/0.04 to 0.24 in.


Product datasheet

XA2EVF5LC

Mounting and Clearance

Mounting


Diameter of Finished Fixing Holes



- (1) Minimum value.
- (2) 40 mm/1.58 in. for Emergency switching off pushbutton only.
- (3) Standard value: Ø 22.3 (0; + 0.4) mm/Ø 0.88 (0; + 0.02) in.

Connections and Schema

Wiring Diagram



(1) LED