Product data sheet

Specifications





TeSys Deca contactor , 4P(2 NO + 2 NC) , AC-1 , <= 440V, 80 A , 240V AC 50 Hz coil

LC1D65008U5

Discontinued on: 10/10/2020

① Discontinued

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[Ie] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	240 V AC 50 Hz

Complementary

Compatibility Code	LC1D
Pole Contact Composition	2 NO + 2 NC
Contact Compatibility	M1
Protective Cover	Without
[Ith] Conventional Free Air Thermal Current	80 A (at 60 °C) for power circuit
Irms Rated Making Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	520 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit 110 A 40 °C - 10 min for power circuit 260 A 40 °C - 1 min for power circuit
Associated Fuse Rating	125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	9.6 W AC-1
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3

Life Is On Schneider

Uimp] Rated Impulse Withstand /oltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 80 A AC-1 at Ue <= 440 V
Control Circuit Type	AC at 50 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.30.6 Uc (-4070 °C):drop-out AC 50 Hz 11.1 Uc (6070 °C):operational AC 50 Hz
nrush Power In Va	160 VA 50 Hz cos phi 0.75 (at 20 °C)
Iold-In Power Consumption In Va	15 VA 50 Hz cos phi 0.3 (at 20 °C)
leat Dissipation	45 W at 50 Hz
Operating Time	419 ms opening 1226 ms closing
Aximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end
Fightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 8 N.m - on screw clamp terminals - cable 2535 mm² hexagonal screw head 4 mm Power circuit: 5 N.m - on screw clamp terminals - cable 125 mm² hexagonal screw head 4 mm
Mounting Support	Plate Rail

Environment

Standards

CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508

Product Certifications	DNV UL GL GOST CCC RINA CSA BV LROS (Lloyds register of shipping)
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Shocks contactor open (8 Gn for 11 ms) Shocks contactor closed (10 Gn for 11 ms) Vibrations contactor opened (2 Gn, 5300 Hz) Vibrations contactor closed (3 Gn, 5300 Hz)
Height	127 mm
Width	85 mm
Depth	125 mm
Net Weight	1.45 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13 cm
Package 1 Width	9.5 cm
Package 1 Length	13.5 cm
Package 1 Weight	1.45 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information