Product datasheet

Specification





Push button, metal, flush, black, Ø22, spring return, unmarked, 1 NO

XB4BA21

Main

Range Of Product	Harmony XB4	
Product Or Component Type	Push-button	
Device Short Name	XB4	
Bezel Material	Chromium plated metal	
Fixing Collar Material	Zamak	
Mounting Diameter	22.5 mm	
Sale Per Indivisible Quantity	1	
Shape Of Signaling Unit Head	Round	
Type Of Operator	spring return	
Operator Profile	Black flush, unmarked	
Head Type	Standard	
Contacts Type And Composition	1 NO	
Contact Operation	Slow-break	
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, 1 x 0.222 x 2.5 mm² without cable end conforming to IEC 60947-1	

Complementary

Height	47 mm	
Width	30 mm	
Depth	52 mm	
Terminals Description Iso N°1	(13-14)NO	
Net Weight	0.08 kg	
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m	
Contacts Usage	Standard contacts	
Positive Opening	Without	
Operating Travel	2.6 mm (NO changing electrical state) 4.3 mm (total travel)	
Operating Force	3.8 N NO changing electrical state	
Mechanical Durability	10000000 cycles	
Tightening Torque	0.81.2 N.m conforming to IEC 60947-1	

Shape Of Screw Head	Cross compatible with Philips no 1 screwdriver	
	Cross compatible with pozidriv No 1 screwdriver	
	Slotted compatible with flat Ø 4 mm screwdriver	
	Slotted compatible with flat Ø 5.5 mm screwdriver	
Contacts Material	Silver alloy (Ag/Ni)	
Short-Circuit Protection	10 A cartridge fuse type gG conforming to IEC 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A conforming to IEC 60947-5-1	
[Ui] Rated Insulation Voltage	600 V (pollution degree 3) conforming to IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1	
[le] Rated Operational Current	3 A at 240 V, AC-15, A600 conforming to IEC 60947-5-1	
	6 A at 120 V, AC-15, A600 conforming to IEC 60947-5-1	
	0.1 A at 600 V, DC-13, Q600 conforming to IEC 60947-5-1	
	0.27 A at 250 V, DC-13, Q600 conforming to IEC 60947-5-1	
	0.55 A at 125 V, DC-13, Q600 conforming to IEC 60947-5-1	
	1.2 A at 600 V, AC-15, A600 conforming to IEC 60947-5-1	
Electrical Durability	1000000 cycles, AC-15, 2 A at 230 V, operating rate <3600 cyc/h, load factor: 0.5	
•	conforming to IEC 60947-5-1 appendix C	
	1000000 cycles, AC-15, 3 A at 120 V, operating rate <3600 cyc/h, load factor: 0.5	
	conforming to IEC 60947-5-1 appendix C	
	1000000 cycles, AC-15, 4 A at 24 V, operating rate <3600 cyc/h, load factor: 0.5	
	conforming to IEC 60947-5-1 appendix C	
	1000000 cycles, DC-13, 0.2 A at 110 V, operating rate <3600 cyc/h, load factor: 0.5	
	conforming to IEC 60947-5-1 appendix C	
	1000000 cycles, DC-13, 0.5 A at 24 V, operating rate <3600 cyc/h, load factor: 0.5	
	conforming to IEC 60947-5-1 appendix C	
Electrical Reliability	Λ < 10exp(-6) at 5 V and 1 mA in clean environment conforming to IEC 60947-5-4	
······································	Λ < 10exp(-8) at 17 V and 5 mA in clean environment conforming to IEC 60947-5-4	
Device Presentation	Complete product	
Environment		
Protective Treatment	тн	
Ambient Air Temperature For Storage	-4070 °C	
Ambient Air Temperature For Operation	-4070 °C	
Overvoltage Category	Class I conforming to IEC 60536	
p Degree Of Protection	IP66 conforming to IEC 60529	
	IP67 IP69	
	IP69 IP69K	
	••	
Nema Degree Of Protection	NEMA 13 NEMA 4X	
lk Degree Of Protection	IK06 conforming to IEC 50102	
Standards	CSA C22.2 No 14	
	IEC 60947-1	
	IEC 60947-5-4	
	IEC 60947-5-1	
	IEC 60947-5-5	
	UL 508	
	JIS C8201-5-1 JIS C8201-1	
Product Contifications		
Product Certifications	GL BV	
	LROS (Lloyds register of shipping) UL listed	
	CSA	
	DNV	
	DIAA	

Vibration Resistance

5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6

Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC
	60068-2-27
	50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC
	60068-2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	5.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.08 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	150
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	12.279 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1200
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	106.232 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



- \boldsymbol{e} : clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.
- (1) Additional row of contacts or double contact.

XB4BA21

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connectors or on Printed Circuit Board

(1)

(2)

Connection by Screw Clamp Terminals or Plug-in

Connection by Faston Connectors



(1) Diameter on finished panel or support

(3)

- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0^{+0.4}$ / 0.88 in. $_0^{+0.016}$)

(4)

- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.