Product datasheet

Specifications





orange complete pilot light Ø22 plain lens with BA9s bulb 230...240V

XB4BV45

Main

| Range Of Product | Harmony XB4 |
|---------------------------------|-------------------------------------|
| Product Or Component Type | Pilot light |
| Device Short Name | XB4 |
| Bezel Material | Chromium plated metal |
| Fixing Collar Material | Zamak |
| Head Type | Standard |
| Mounting Diameter | 22.5 mm |
| Sale Per Indivisible Quantity | 1 |
| Shape Of Signaling Unit Head | Round |
| Cap/Operator Or Lens Colour | Orange |
| Operator Additional Information | With plain lens |
| Light Source | Incandescent |
| Bulb Base | BA 9s |
| Light Block Supply | Via integral transformer 1.2 VA 6 V |
| [Us] Rated Supply Voltage | 230240 V AC at 50/60 Hz |

Complementary

| Height | 47 mm |
|---|--|
| Width | 30 mm |
| Depth | 78 mm |
| Terminals Description Iso N°1 | (X1-X2)PL |
| Net Weight | 0.152 kg |
| Resistance To High Pressure Washer | 7000000 Pa at 55 °C, distance : 0.1 m |
| Connections - Terminals | Screw clamp terminals, <= 2 x 1.5 mm ² with cable end conforming to IEC 60947-1 Screw clamp terminals, 1 x 0.222 x 2.5 mm ² without cable end conforming to IEC 60947-1 |
| [Ui] Rated Insulation Voltage | 600 V (pollution degree 3) conforming to IEC 60947-1 |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV conforming to IEC 60947-1 |
| Signalling Type | Steady |
| Device Presentation | Complete product |

Environment

| Protective Treatment | тн |
|--|--|
| Ambient Air Temperature For Storage | -4070 °C |
| Ambient Air Temperature For Operation | -4055 °C |
| Electrical Shock Protection Class | Class I conforming to IEC 60536 |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 IP67 IP69 IP69K |
| Nema Degree Of Protection | NEMA 13 NEMA 4X |
| Ik Degree Of Protection | IK06 conforming to IEC 50102 |
| Standards | IEC 60947-1 IEC 60947-5-5 IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-4 UL 508 JIS C8201-5-1 JIS C8201-1 |
| Product Certifications | UL listed CSA |
| Vibration Resistance | 5 gn (f= 12500 Hz) conforming to IEC 60068-2-6 |
| Shock Resistance | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

Packing Units

| U | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.4 cm |
| Package 1 Width | 4.8 cm |
| Package 1 Length | 3.4 cm |
| Package 1 Weight | 146.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 8.8 cm |
| Package 2 Width | 26.5 cm |
| Package 2 Length | 3.4 cm |
| Package 2 Weight | 735.0 g |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 50 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 7.788 kg |
| | |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes


Certifications & Standards

| Reach Regulation | REACh Declaration | | | |
|--------------------------|---|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | | |
| China Rohs Regulation | China RoHS declaration | | | |
| Environmental Disclosure | Product Environmental Profile | | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins | | | |
| Circularity Profile | End of Life Information | | | |

Product datasheet

Dimensions Drawings

Dimensions



e : clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

| a in mm | a in in. | b in mm | b in in. | c in mm | c in in. |
|---------|----------|---------|----------|---------|----------|
| 66 | 2.60 | 30 | 1.18 | 46.5 | 1.83 |

Product datasheet

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

