# **Product data sheet**

Specification





## contactor, TeSys K, 4P(4NO),AC-1, 440V, 20A, 12V DC coil, screw clamp terminals

LP1K09004JD

### Main

Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LP1K
Contactor Application	Resistive load

### Complementary

Complementary	
Utilisation Category	AC-1
Poles Description	4P
Power Pole Contact Composition	4 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC <= 400 Hz Signalling circuit: <= 690 V AC <= 400 Hz
[le] Rated Operational Current	20 A (at <60 °C) at <= 690 V AC AC-1 for power circuit
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	12 V DC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit
Irms Rated Making Capacity	110 A AC for power circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	90 A 50 °C - 1 s for power circuit 85 A 50 °C - 5 s for power circuit 80 A 50 °C - 10 s for power circuit 60 A 50 °C - 30 s for power circuit 45 A 50 °C - 1 min for power circuit 40 A 50 °C - 3 min for power circuit 20 A 50 °C - >= 15 min for power circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit 25 A aM for power circuit
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to UL 508 Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V conforming to CSA C22.2 No 14
Inrush Power In W	3 W (at 20 °C)

Hold-In Power Consumption In W	3 W at 20 °C
Heat Dissipation	1.3 W
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <50 °C) Drop-out: >= 0.10 Uc (at <50 °C)
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end Screw clamp terminals 2 cable(s) 1.54 mm²solid Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.5 mm²flexible with cable end
Maximum Operating Rate	3600 cyc/h
Mounting Support	Plate Rail
Tightening Torque	0.81.3 N.m - on screw clamp terminals Philips No 2 0.81.3 N.m - on screw clamp terminals flat Ø 6 mm 0.81.3 N.m - on screw clamp terminals pozidriv No 2
Operating Time	3040 ms coil energisation and NO closing 10 ms coil de-energisation and NO opening
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	10 Mcycles
Electrical Durability	0.16 Mcycles 20 A AC-1 at Ue <= 690 V
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.225 kg

## **Environment**

Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Ip Degree Of Protection	IP2X
Ambient Air Temperature For Operation	-2550 °C
Ambient Air Temperature For Storage	-5080 °C
Operating Altitude	2000 m without derating
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

## **Packing Units**

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	6.400 cm
Package 1 Width	6.100 cm
Package 1 Length	4.800 cm
Package 1 Weight	218.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.160 kg

## Contractual warranty

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information