Product data sheet

Specification





compact smart relay, Zelio Logic SR2 SR3, 12 IO, 12V DC, clock, display

SR2B121JD

Main

| Range Of Product | Zelio Logic | |
|---------------------------|---------------------|--|
| Product Or Component Type | Compact smart relay | |

Complementary

| Complementary | |
|--------------------------------|--|
| Local Display | With |
| Number Or Control Scheme Lines | 0240 with ladder programming 0500 with FBD programming |
| Cycle Time | 690 ms |
| Backup Time | 10 years at 25 °C |
| Clock Drift | 12 min/year at 055 °C 6 s/month at 25 °C |
| Checks | Program memory on each power up |
| [Us] Rated Supply Voltage | 12 V DC |
| Supply Voltage Limits | 10.414.4 V |
| Maximum Supply Current | 120 mA (without extension) |
| Power Dissipation In W | 1.5 W without extension |
| Reverse Polarity Protection | With |
| Discrete Input Number | 8 conforming to IEC 61131-2 Type 1 |
| Discrete Input Type | Resistive |
| Discrete Input Voltage | 12 V DC |
| Discrete Input Current | 4 mA |
| Counting Frequency | 1 kHz for discrete input |
| Voltage State 1 Guaranteed | >= 7 V for IBIG used as discrete input circuit >= 5.6 V for I1IA and IHIR discrete input circuit |
| Voltage State 0 Guaranteed | <= 3 V for IBIG used as discrete input circuit <= 2.4 V for I1IA and IHIR discrete input circuit |
| Current State 1 Guaranteed | >= 2 mA (I1IA and IHIR discrete input circuit) >= 0.5 mA (IBIG used as discrete input circuit) |
| Current State 0 Guaranteed | <= 0.2 mA (IBIG used as discrete input circuit) <= 0.9 mA (I1IA and IHIR discrete input circuit) |
| Input Compatibility | 3-wire proximity sensors PNP for discrete input |
| Analogue Input Number | 4 |
| Analogue Input Type | Common mode |
| Analogue Input Range | 010 V 012 V |

| Maximum Permissible Voltage | 14.4 V for analogue input circuit |
|---|--|
| Analogue Input Resolution | 8 bits at maximum voltage |
| Lsb Value | 39 mV for analogue input circuit |
| Conversion Time | Smart relay cycle time for analogue input circuit |
| Conversion Error | +/- 5 % at 25 °C for analogue input circuit +/- 6.2 % at 55 °C for analogue input circuit |
| Repeat Accuracy | +/- 2 % at 55 °C for analogue input circuit |
| Operating Distance | 10 m between stations, with screened cable (sensor not isolated) for analogue input circuit |
| Input Impedance | 14 kOhm for IBIG used as analogue input circuit 14 kOhm for IBIG used as discrete input circuit 2.7 kOhm for I1IA and IHIR discrete input circuit |
| Number Of Outputs | 4 relay |
| Output Voltage Limits | 24250 V AC (relay output) 530 V DC (relay output) |
| Contacts Type And Composition | NO for relay output |
| Output Thermal Current | 8 A for all 4 outputs for relay output |
| Electrical Durability | AC-12: 500000 cycles at 230 V, 1.5 A for relay output conforming to IEC 60947-5-1 AC-15: 500000 cycles at 230 V, 0.9 A for relay output conforming to IEC 60947-5-1 DC-12: 500000 cycles at 24 V, 1.5 A for relay output conforming to IEC 60947-5-1 DC-13: 500000 cycles at 24 V, 0.6 A for relay output conforming to IEC 60947-5-1 |
| Switching Capacity In Ma | >= 10 mA at 12 V (relay output) |
| Operating Rate In Hz | 0.1 Hz (at le) for relay output 10 Hz (no load) for relay output |
| Mechanical Durability | 10000000 cycles for relay output |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV conforming to EN/IEC 60947-1 and EN/IEC 60664-1 |
| Clock | With |
| Response Time | 10 ms (from state 0 to state 1) for relay output 5 ms (from state 1 to state 0) for relay output |
| Connections - Terminals | Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 25AWG 14) solid Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) solid Screw terminals, 2 x 0.252 x 0.75 mm² (AWG 24AWG 18) flexible with cable end |
| Tightening Torque | 0.5 N.m |
| Overvoltage Category | III conforming to IEC 60664-1 |
| Net Weight | 0.25 kg |

Environment

| Immunity To Microbreaks | 1 ms repeated 20 times |
|-------------------------|------------------------|
| Product Certifications | C-Tick |
| | UL |
| | CSA |
| | GOST |
| | GL |

| Standards | IEC 61000-4-11 IEC 60068-2-6 Fc IEC 61000-4-12 IEC 61000-4-2 level 3 IEC 61000-4-5 IEC 61000-4-3 IEC 61000-4-4 level 3 IEC 60068-2-27 Ea IEC 61000-4-6 level 3 |
|---------------------------------------|--|
| Ip Degree Of Protection | IP20 (terminal block) conforming to IEC 60529 IP40 (front panel) conforming to IEC 60529 |
| Environmental Characteristic | EMC directive conforming to IEC 61000-6-2 EMC directive conforming to IEC 61000-6-3 EMC directive conforming to IEC 61000-6-4 EMC directive conforming to IEC 61131-2 zone B Low voltage directive conforming to IEC 61131-2 |
| Disturbance Radiated/Conducted | Class B conforming to EN 55022-11 group 1 |
| Pollution Degree | 2 conforming to IEC 61131-2 |
| Ambient Air Temperature For Operation | -2040 °C in non-ventilated enclosure conforming to IEC 60068-2-1 and IEC 60068-2-2 -2055 °C conforming to IEC 60068-2-1 and IEC 60068-2-2 |
| Ambient Air Temperature For Storage | -4070 °C |
| Operating Altitude | 2000 m |
| Maximum Altitude Transport | 3048 m |
| Relative Humidity | 95 % without condensation or dripping water |

Packing Units

| _ | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.8 cm |
| Package 1 Width | 9.0 cm |
| Package 1 Length | 10.0 cm |
| Package 1 Weight | 239.0 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 30 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 7.775 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free | |
|----------|----------------------------|-----|
| ② | Rohs Exemption Information | Yes |
| | Pvc Free | |

Certifications & Standards


| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |

26/04/2024

Dimensions Drawings


Compact and Modular Smart Relays

Mounting on 35 mm/1.38 in. DIN Rail




(1) With SR2USB01 or SR2BTC01

Screw Fixing (Retractable Lugs)



(1) With SR2USB01 or SR2BTC01


Position of Display



Connections and Schema


Compact and Modular Smart Relays

Connection of Smart Relays on DC Supply



- (1) 1 A quick-blow fuse or circuit-breaker.
- (2) Fuse or circuit-breaker.
- (3) Inductive load.
- (4) Q9 and QA: 5 A (max. current in terminal C: 10 A).

Discrete Input Used for 3-Wire Sensors




(1) 1 A quick-blow fuse or circuit-breaker.

Performance Curves

Compact and Modular Smart Relays

Electrical Durability of Relay Outputs

(in millions of operating cycles, conforming to IEC/EN 60947-5-1) DC-12 (1)




X: Current (A)

Y: Millions of operating cycles

(1) DC-12: control of resistive loads and of solid state loads isolated by opto-coupler, L/R ≤ 1 ms.

DC-13 (1)



X: Current (A)

Y: Millions of operating cycles

(1) DC-13: switching electromagnets, $L/R \le 2 \times (Ue \times Ie)$ in ms, Ue: rated operational voltage, Ie: rated operational current (with a protection diode on the load, DC-12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles).