# **Product datasheet**

Specification





# Preventa safety module XPSAF, emergency stop, 24VAC DC

XPSAFL5130

! Discontinued on: 31-Dec-2023

! End-of-service on: 31-Dec-2023

① Discontinued - Service only

#### Main

mam	
Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAF
Safety Module Application	For emergency stop, switch and safety light curtain monitoring
Function Of Module	Monitoring of electro-sensitive protection equipment (ESPE)  Monitoring of a movable guard  Emergency stop with 2 NC contacts monitoring 2-channel wiring  Emergency stop monitoring 1-channel wiring  Multiple emergency stop monitoring 2-channel wiring
Safety Level	Can reach PL e/category 4 conforming to ISO 13849-1 Can reach SILCL 3 conforming to IEC 62061
Safety Reliability Data	DC > 99 % conforming to ISO 13849-1 MTTFd = 172.1 years conforming to ISO 13849-1 PFHd = 5.61E-9 1/h conforming to IEC 62061
Type Of Start	Unmonitored
Connections - Terminals	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² flexible with cable end, with double bezel  Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² solid with cable end, with double bezel  Captive screw clamp terminals, 1 x 0.251 x 1.5 mm² flexible with cable end, with double bezel  Captive screw clamp terminals, 1 x 0.251 x 2.5 mm² flexible with cable end, with double bezel  Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² flexible with cable end, with double bezel  Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² solid with cable end, with double bezel  Captive screw clamp terminals, 2 x 0.142 x 1 mm² flexible with cable end, with double bezel  Captive screw clamp terminals, 2 x 0.252 x 1 mm² flexible with cable end, with double bezel  Captive screw clamp terminals, 2 x 0.52 x 1.5 mm² flexible with cable end, with double bezel
Output Type	Relay instantaneous opening, 3 NO circuit(s), volt-free
Number Of Additional Circuits	0
[Us] Rated Supply Voltage	24 V AC - 1510 % 24 V DC - 1510 %

# Complementary

Synchronisation Time Between Inputs	Unlimited
Supply Frequency	50/60 Hz
Maximum Power Consumption In Va	5 VA AC
Input Protection Type	Internal, electronic

25-Apr-2024 Life Is On Schneider

[Uc] Control Circuit Voltage	24 V
Maximum Line Resistance	90 Ohm
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Output Thermal Current	6 A per relay for relay output
[Ith] Conventional Free Air Thermal Current	18 A
Associated Fuse Rating	4 A gG or gL for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	10 mA for relay output
Minimum Output Voltage	17 V for relay output
Maximum Response Time On Input Open	40 ms
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local Signalling	3 LEDs
Current Consumption	30 mA at 24 V AC on power supply
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.25 kg

## **Environment**

Standards	ISO 13850 IEC 60947-5-1 EN/IEC 61496-1 (type 4) IEC 60204-1 EN 1088/ISO 14119
Product Certifications	TÜV UL CSA
Ip Degree Of Protection	IP20 (terminals) conforming to IEC 60529 IP40 (enclosure) conforming to IEC 60529
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For Storage	-2585 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	10.5 cm
Package 1 Length	12.1 cm
Package 1 Weight	252.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	16
Package 2 Height	15.0 cm

Package 2 Width	15.0 cm	
Package 2 Length	40.0 cm	
Package 2 Weight	4 395 kg	

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## **Product datasheet**

### XPSAFL5130

#### **Dimensions Drawings**

#### **Dimensions**

