

Produkta datu lapa

Specifikācijas



Kontaktors, TeSys Deca,
3P(3NO), AC-3/AC-3e, <=440V,
9A, 24V DC spole, skrūvju spaiļes

LC1D09BD

Galvenā

Produkta Sērija	TeSys Deca
Produkta Vai Sastāvdaļas Veids	Contactor
Ierīces Īsais Nosaukums	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Polu Skaits	3P
[Ue] Nominālais Darbības Spriegums	Strāvas ķēde: <= 690 V AC 25...400 Hz Strāvas ķēde: <= 300 V DC
[Ie] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for strāvas ķēde 25 A (at <60 °C) at <= 440 V AC AC-1 for strāvas ķēde 9 A (at <60 °C) at <= 440 V AC AC-3e for strāvas ķēde
[Uc] Control Circuit Voltage	24 V DC

Papildinošs

Motor Power Kw	2,2 kW at 220...230 V AC 50/60 Hz (AC-3) 4 kW at 380...400 V AC 50/60 Hz (AC-3) 4 kW at 415...440 V AC 50/60 Hz (AC-3) 5,5 kW at 500 V AC 50/60 Hz (AC-3) 5,5 kW at 660...690 V AC 50/60 Hz (AC-3) 2,2 kW at 400 V AC 50/60 Hz (AC-4) 2,2 kW at 220...230 V AC 50/60 Hz (AC-3e) 4 kW at 380...400 V AC 50/60 Hz (AC-3e) 4 kW at 415...440 V AC 50/60 Hz (AC-3e) 5,5 kW at 500 V AC 50/60 Hz (AC-3e) 5,5 kW at 660...690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	1 hp at 230/240 V AC 50/60 Hz for 1 fāze motors 2 hp at 200/208 V AC 50/60 Hz for 3 fāzes motors 2 hp at 230/240 V AC 50/60 Hz for 3 fāzes motors 5 hp at 460/480 V AC 50/60 Hz for 3 fāzes motors 7,5 hp at 575/600 V AC 50/60 Hz for 3 fāzes motors 0,33 hp at 115 V AC 50/60 Hz for 1 fāze motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	25 A (at 60 °C) for strāvas ķēde 10 A (at 60 °C) for signalling circuit
Irms Rated Making Capacity	250 A at 440 V for strāvas ķēde conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for strāvas ķēde conforming to IEC 60947

Ir sasniegta maksimālā salīdzināmo produktu skaits. Lūdzu, atveriet sadalī. Salīdzināt produktus #SAITE# un izvēlēties kādu produktu, lai turpinātu.

[Icw] Rated Short-Time Withstand Current	105 A 40 °C - 10 s for strāvas ķēde 210 A 40 °C - 1 s for strāvas ķēde 30 A 40 °C - 10 min for strāvas ķēde 61 A 40 °C - 1 min for strāvas ķēde 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 25 A gG at <= 690 V coordination type 1 for strāvas ķēde 20 A gG at <= 690 V coordination type 2 for strāvas ķēde
Average Impedance	2,5 mhm - lth 25 A 50 Hz for strāvas ķēde
Power Dissipation Per Pole	1,56 W AC-1 0,2 W AC-3 0,2 W AC-3e
[Ui] Rated Insulation Voltage	Strāvas ķēde 690 V IEC 60947-4-1 Strāvas ķēde 600 V CSA Strāvas ķēde 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Pārsprieguma Kategorija	III
Piesārņojuma Pakāpe	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cikli contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cikli contactor with mechanical load EN/ISO 13849-1
Mehāniskā Izturība	30 M cikli
Electrical Durability	0,6 M cikli 25 A AC-1 <= 440 V 2 M cikli 9 A AC-3 <= 440 V 2 M cikli 9 A AC-3e <= 440 V
Control Circuit Type	DC standard
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.1...0.25 Uc -40...70 °C drop-out DC 0.7...1.25 Uc -40...60 °C operational DC 1...1.25 Uc 60...70 °C operational DC
Inrush Power In W	5,4 W 20 °C)
Hold-In Power Consumption In W	5,4 W 20 °C
Operating Time	63 ±15 % ms closing 20 ±20 % ms opening
Time Constant	28 ms
Maximum Operating Rate	3600 cikls/h 60 °C

Connections - Terminals	Strāvas ķēde: screw clamp terminals 1 1...4 mm² - cable stiffness: elastīgs without cable end Strāvas ķēde: screw clamp terminals 2 1...4 mm² - cable stiffness: elastīgs without cable end Strāvas ķēde: screw clamp terminals 1 1...4 mm² - cable stiffness: elastīgs with cable end Strāvas ķēde: screw clamp terminals 2 1...2,5 mm² - cable stiffness: elastīgs with cable end Strāvas ķēde: screw clamp terminals 1 1...4 mm² - cable stiffness: ciets without cable end Strāvas ķēde: screw clamp terminals 2 1...4 mm² - cable stiffness: ciets without cable end Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: elastīgs without cable end Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: elastīgs without cable end Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: elastīgs with cable end Control circuit: screw clamp terminals 2 1...2,5 mm² - cable stiffness: elastīgs with cable end Control circuit: screw clamp terminals 1 1...4 mm² - cable stiffness: ciets without cable end Control circuit: screw clamp terminals 2 1...4 mm² - cable stiffness: ciets without cable end
Tightening Torque	Strāvas ķēde 1,7 N.m screw clamp terminals flat Ø 6 mm Strāvas ķēde 1,7 N.m screw clamp terminals Philips No 2 Control circuit 1,7 N.m screw clamp terminals flat Ø 6 mm Control circuit 1,7 N.m screw clamp terminals Philips No 2 Control circuit 1,7 N.m screw clamp terminals pozidriv No 2 Strāvas ķēde 1,7 N.m screw clamp terminals pozidriv No 2
Papildkontakta Veids	1 NO + 1 NC
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25...400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1,5 ms on de-energisation between NC and NO contact 1,5 ms on energisation between NC and NO contact
Montāžas Stiprinājums	Plāksne Rail

Vide

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Produkta Sertifikācija	LROS (Lloyds register of shipping) CSA UL GOST DNV CCC GL BV RINA UKCA
Ip Degree Of Protection	IP20 priekšpuse IEC 60529
Protective Treatment	THIEC 60068-2-30
Climatic Withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat

Permissible Ambient Air Temperature Around The Device	-40...60 °C 60...70 °C with derating
Operating Altitude	0...3000 m
Fire Resistance	850 °C IEC 60695-2-1
Flame Retardance	V1 UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5...300 Hz) Vibrations contactor closed 4 Gn, 5...300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)
Augstums	77 mm
Platums	45 mm
Dziļums	95 mm
Neto Svars	0,48 kg

Iepakojšanas vienības

Pirmā Iepakojuma Vienības Tips	PCE
Vienību Skaits 1. Iepakojumā	1
1. Iepakojuma Augstums	5,000 cm
1. Iepakojuma Platums	9,200 cm
1. Iepakojuma Garums	11,100 cm
1. Iepakojuma Svars	523,000 g
Otrā Iepakojuma Vienības Tips	S02
Vienību Skaits 2. Iepakojumā	15
2. Iepakojuma Augstums	15,000 cm
2. Iepakojuma Platums	30,000 cm
2. Iepakojuma Garums	40,000 cm
2. Iepakojuma Svars	8,160 kg
Trešā Iepakojuma Vienības Tips	P06
Vienību Skaits 3. Iepakojumā	240
3. Iepakojuma Augstums	75,000 cm
3. Iepakojuma Platums	60,000 cm
3. Iepakojuma Garums	80,000 cm
3. Iepakojuma Svars	137,280 kg

Līguma garantija

Garantija	18 months
-----------	-----------

Ilgtspējības nodaļa

Green Premium™ marķējums ir Schneider Electric apņemšanās piegādāt produktus ar savā klasē labākajiem vides rādītājiem. Green Premium apliecina atbilstību jaunākajiem noteikumiem, pārredzamību par ietekmi uz vidi, kā arī aprites un zema CO₂ produktiem.

Produktu ilgtspējības novērtēšanas rokasgrāmata ir baltā grāmata, kurā izskaidroti globālie ekomarķējuma standarti un tas, kā interpretēt vides deklarācijas.

[Rokasgrāmata produkta ilgtspējas novērtēšanai >](#)



Pārredzamība RoHS/REACH

Labklājības veikspēja

 Nesatur Dzīvsudrabu

 Informācija Par Rohs Izņēmumiem [Jā](#)


 Nesatur Pvh

Sertifikācijas un standarti

Reach Regula	REACH deklarācija
Es Rohs Direktīva	Atbilst izņēmumiem
Ķīnas Rohs Regula	Ķīnas RoHS deklarācija Produkts neietilpst Ķīnas RoHS ietvaros. Vietas deklarācijai informatīva nozīme.
Vides Informācijas Publiskošana	Produkta ietekme uz vidi
Cirkularitātes Profils	Informācija par ekspluatācijas izbeigšanu

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D09...D18	D093...D123	D099...D129
b		77	99	80
c	without cover or add-on blocks	93	93	93
	with cover, without add-on blocks	95	95	95
c1	with LAD N or C (2 or 4 contacts)	126	126	126
c2	with LA6 DK10	138	138	138
c3	with LAD T, R, S	146	146	146
	with LAD T, R, S and sealing cover	150	150	150

Connections and Schema

Wiring

