



## Pārskats

Piegādes laiks	Usually in Stock
----------------	------------------

## General

Provided equipment	CD with software Communication cable Documentation CD Installation guide Removable support feet USB cable Warranty card
Product web sub-family	Lithium-Ion
Number of tare power	80 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	S

## Physical

Cable length	1,83 m
Number of rack unit	3U
Colour	Black
Depth	63,9 cm
Height	12,8 cm
Mounting position	Vertical
Mounting preference	No preference
Net weight	30,5 kg
Mounting mode	Rack-mounted with kit
Two post mountable	0

USB compatible	Yes
Width	43,2 cm

## Input

Network frequency	40...70 Hz auto-sensing
Plug standard	IEC 60320 C20
Input voltage limits	160...275 V
Inputvolt_other	220 V 240 V
Number of cables	1
Input voltage	230 V

## Output

Rated power in W	2700 W
Maximum configurable power in W	2700 W
Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Outputvolt_other	220 V 240 V
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Nb of power socket outlets	6 IEC 60320 C13 2 IEC 60320 C19
Bypass type	Built-in bypass
Graph display	1
Output voltage	230 V
Maximum configurable power in VA	3000 VA
Rated power in VA	3000 VA

## Conformance

Product certifications	CE EAC
------------------------	-----------

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0,00...15240,00 m
Acoustic level	50 dBA
Heat dissipation	317 Btu/h
Show note OP temperature	No
IP degree of protection	IP20

## Batteries & Runtime

Battery type	Li-Ion (Lithium-Ion)
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 h
Liquid value	0

Battery curve	L1
Battery charger power	158 W rated
Battery power in VAH	605 VAh capacity 632 VAh runtime
Battery life	5...10 year(s)
Battery option	XBP48RM1U2-LI 1 1264 VAh XBP48RM1U2-LI 2 1896 VAh XBP48RM1U2-LI 3 2528 VAh XBP48RM1U2-LI 4 3160 VAh XBP48RM1U2-LI 5 3792 VAh XBP48RM1U2-LI 6 4424 VAh XBP48RM1U2-LI 7 5056 VAh XBP48RM1U2-LI 8 5688 VAh
Extended runtime	1

## Communications & Management

Free slots	0
Preinstalled device	Network management card 2 with environmental monitoring
Control panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms prioritized by severity
Emergency power off	Yes

## Surge Protection and Filtering

Surge energy rate	432 J
-------------------	-------

## Packing Units

Iepakojuma 1 svars	41,4 kg
Iepakojuma 1 augstums	24,5 cm
Iepakojuma 1 platums	60 cm
Iepakojuma 1 garums	87 cm
Vienību skaits iepakojumā 3	12

## Offer Sustainability

Ilgspējīgs piedāvājuma statuss	Green Premium izstrādājums
REACH regula	<a href="#">REACH deklarācija</a>
ES RoHS direktīva	Atbilstīgs <a href="#">ES RoHS deklarācija</a>
Nesatur dzīvsudrabu	Jā
Informācija par RoHS izņēmumiem	<a href="#">Jā</a>
Vides informācijas publiskošana	<a href="#">Produkta ietekme uz vidi</a>
Cirkularitātes profils	<a href="#">Informācija par ekspluatācijas izbeigšanu</a>
Optimizēta energoefektivitāte	Energoefektīvs produkts

## Contractual warranty

Garantija	5 year repair or replace
-----------	--------------------------