# **Product datasheet**

Specification





# 15A 250V 1 Gang 3 Round Pin Switched Socket, White

A3G15\_15\_WE\_G11

### Main

| Range                         | Affle Plus            |  |
|-------------------------------|-----------------------|--|
| Product Or Component Type     | Switched socket       |  |
| Device Application            | Switch & socket       |  |
| Device Presentation           | Mechanism             |  |
| Outlet Poles Configuration    | 3P with shutter       |  |
| Outlet Standard Description   | With earthing contact |  |
| Outlet Standard Deviation     | BS 1363               |  |
| Type Of Packing               | Flow-pack             |  |
| Sale Per Indivisible Quantity | 1                     |  |
| Number Of Terminals           | 3                     |  |

## Complementary

| Joinplomontal y   |                                 |  |
|---|---------------------------------|--|
| Socket Number   | 1                               |  |
| Device Mounting   | Flush                           |  |
| Fixing Mode   | Screw                           |  |
| Surface Finish  | Glossy                          |  |
| Surface Treatment   | Untreated mechanism cover       |  |
| Rated Current   | 15 A socket-outlet              |  |
| Je] Rated Operational Voltage 250 V AC 50/60 Hz   |                                 |  |
| Service Life In Cycles  | 15000 cycles                    |  |
| Electrical Durability   | rical Durability 5000 cycles    |  |
| Connections - Terminals   | ons - Terminals Pillar terminal |  |
| crewdriver Shape Philips No 2   |                                 |  |
| Number Of Cables  | 2                               |  |
| Clamping Connection Capacity  2.54 mm² for rigid cable(s)  2.54 mm² for stranded cable(s)  2.54 mm² for flexible cable(s) |                                 |  |
| Wire Stripping Length   | 14 mm                           |  |
| Material  | PC (polycarbonate)<br>Brass     |  |
| Height  | 86 mm                           |  |
| Width   | 86 mm                           |  |
| Depth   | 33.6 mm                         |  |

| Embedding Depth | 23.7 mm |  |
|-----------------|---------|--|
| Net Weight      | 0.07 ka |  |

## **Environment**

| Ambient Air Temperature For Storage   | -560 °C           |
|---------------------------------------|-------------------|
| Ambient Air Temperature For Operation | -545 °C           |
| Relative Humidity                     | 095 %             |
| Standards                             | BS 546<br>MS 1577 |
| Product Certifications                | SIRIM             |
| Ip Degree Of Protection               | IP20              |

# **Packing Units**

| _                            |            |
|------------------------------|------------|
| Unit Type Of Package 1       | PCE        |
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 3.5 cm     |
| Package 1 Width              | 8.6 cm     |
| Package 1 Length             | 8.6 cm     |
| Package 1 Weight             | 78.0 g     |
| Unit Type Of Package 2       | CAR        |
| Number Of Units In Package 2 | 10         |
| Package 2 Height             | 9.5 cm     |
| Package 2 Width              | 15.0 cm    |
| Package 2 Length             | 19.0 cm    |
| Package 2 Weight             | 786.0 g    |
| Unit Type Of Package 3       | PAL        |
| Number Of Units In Package 3 | 1920       |
| Package 3 Height             | 100.0 cm   |
| Package 3 Width              | 80.0 cm    |
| Package 3 Length             | 120.0 cm   |
| Package 3 Weight             | 158912.0 g |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Toxic Heavy Metal Free     |     |
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration                        |
|--------------------------|--|
| Eu Rohs Directive        | Compliant EU RoHS Declaration            |
| China Rohs Regulation    | China RoHS declaration                   |
| Environmental Disclosure | Product Environmental Profile            |
| Circularity Profile      | No need of specific recycling operations |