Product data sheet

Specifications





circuit breaker Easypact EZCV250N - TMD - 125 A - 4 poles 4d

EZCV250N4125

Main

Range Of Product	EasyPact	
Product Or Component Type	Circuit breaker	
Device Short Name	Easypact EZCV250N	
Circuit Breaker Name	Easypact EZCV250N	
Device Application	Distribution	
Poles Description	4P	
Protected Poles Description	4t	
Network Type	AC	
Network Frequency	50/60 Hz	
[In] Rated Current	125 A at 40 °C	
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz conforming to IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2	
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz conforming to IEC 60947-2	
Breaking Capacity Code	Ν	
Breaking Capacity	20 kA lcu at 440 V AC 50/60 Hz conforming to IEC 60947-2 85 kA lcu at 220240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA lcu at 380415 V AC 50/60 Hz conforming to IEC 60947-2	
[Ics] Rated Service Breaking Capacity	10 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 42.5 kA at 220240 V AC 50/60 Hz conforming to IEC 60947-2 12.5 kA at 380415 V AC 50/60 Hz conforming to IEC 60947-2	
Suitability For Isolation	Yes conforming to IEC 60947-2	
Utilisation Category	Category A	
Trip Unit Name	TM-D	
Trip Unit Technology	Thermal-magnetic	
Trip Unit Rating	125 A at 40 °C	
Protection Type	Overload protection Short-circuit protection Earth-leakage protection	
Pollution Degree	3 conforming to IEC 60947	

Complementary

Control Type	Toggle	
Mounting Mode	Fixed	
Mounting Support	Backplate	

List Price displayed is VAT EXCLUSIVE.

Upside Connection	Front	
Downside Connection	Front	
Mechanical Durability	10000 cycles	
Electrical Durability	Category A: 5000 cycles 415 V AC 50/60 Hz conforming to IEC 60947-2	
Connection Pitch	35 mm	
Local Signalling	Positive contact indication	
Neutral Protection Setting	Without protection	
Earth-Leakage Protection	With	
Height	165 mm	
Width	140 mm	
Depth	68 mm	

Environment

Standards	GB/T 14048.2 JIS C8201-2-2 EN/IEC 60947-1	
	EN/IEC 60947-2	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to EN 50102	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-3585 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	14.5 cm
Package 1 Length	18.5 cm
Package 1 Weight	2.52 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	15.607 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	96
Package 3 Height	72.0 cm
Package 3 Width	125.0 cm
Package 3 Length	96.0 cm
Package 3 Weight	241.92 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh


Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations Circularity Profile

Dimensions Drawings



Assembly



6

Performance Curves

