Product datasheet

Specifications





variable speed drive ATV610 - 37 kW/50 HP - 380...415 V - IP20

ATV610D37N4

Training Objectives: Compliant

Main

IVIAIII	
Range Of Product	Easy Altivar 610
Product Or Component Type	Variable speed drive
Product Specific Application	Fan, pump, compressor, conveyor
Device Short Name	ATV610
Variant	Standard version
Product Destination	Asynchronous motors Synchronous motors
Mounting Mode	Cabinet mount
Emc Filter	Integrated conforming to IEC 61800-3 category C3 with 50 m
Ip Degree Of Protection	IP20
Type Of Cooling	Forced convection
Supply Frequency	5060 Hz +/-5 %
Network Number Of Phases	3 phases
[Us] Rated Supply Voltage	380460 V - 1510 %
Motor Power Kw	37 kW for normal duty 30 kW for heavy duty
Motor Power Hp	50 hp for normal duty 40 hp for heavy duty
Line Current	76.6 A at 380 V (normal duty) 68.3 A at 460 V (normal duty) 65.8 A at 380 V (heavy duty) 56.8 A at 460 V (heavy duty)
Prospective Line Isc	22 kA
Apparent Power	54.4 kVA at 460 V (normal duty) 45.2 kVA at 460 V (heavy duty)
Continuous Output Current	74.5 A at 4 kHz for normal duty 59.6 A at 4 kHz for heavy duty
Maximum Transient Current	82 A during 60 s (normal duty) 89.4 A during 60 s (heavy duty)
Asynchronous Motor Control Profile	Constant torque standard Optimized torque mode Variable torque standard
Output Frequency	0.1500 Hz
Nominal Switching Frequency	4 kHz
Switching Frequency	212 kHz adjustable
Number Of Preset Speeds	16 preset speeds

Communication Port Protocol	Modbus serial
Option Card	Slot A: communication card, Profibus DP V1 Slot A: digital or analog I/O extension card Slot A: relay output card

Complementary

Complementary		
Output Voltage	<= power supply voltage	
Motor Slip Compensation	sation Can be suppressed Adjustable Not available in permanent magnet motor law	
	Automatic whatever the load	
Acceleration And Deceleration Ramps	S, U or customized Linear adjustable separately from 0.01 to 9000 s	
Braking To Standstill	By DC injection	
Protection Type	Thermal protection: motor	
	Motor phase break: motor	
	Thermal protection: drive	
	Overheating: drive	
	Overcurrent between output phases and earth: drive	
	Overload of output voltage: drive	
	Short-circuit protection: drive	
	Motor phase break: drive	
	Overvoltages on the DC bus: drive	
	Line supply overvoltage: drive	
	Line supply undervoltage: drive	
	Line supply phase loss: drive	
	Overspeed: drive	
	Break on the control circuit: drive	
Frequency Resolution	Display unit: 0.1 Hz Analog input: 0.012/50 Hz	
Electrical Connection	Control, screw terminal: 0.51.5 mm²	
	Line side, screw terminal: 3550 mm²	
	Motor, screw terminal: 3550 mm ²	
Connector Type	1 RJ45 (on the remote graphic terminal) for Modbus serial	
Physical Interface	2-wire RS 485 for Modbus serial	
Transmission Frame	RTU for Modbus serial	
Transmission Rate	4.8, 9.6, 19.2, 38.4 kbit/s for Modbus serial	
Type Of Polarization	No impedance for Modbus serial	
Number Of Addresses	1247 for Modbus serial	
Method Of Access	Slave	
Supply	External supply for digital inputs: 24 V DC (1930 V), <1.25 mA, protection type:	
	overload and short-circuit protection	
	Internal supply for reference potentiometer (1 to 10 kOhm): 10.5 V DC +/- 5 %, <10	
	mA, protection type: overload and short-circuit protection	
Land Cinnalling		
Local Signalling	2 LEDs for local diagnostic	
	1 LED (yellow) for embedded communication status	
	2 LEDs (dual colour) for communication module status	
	1 LED (red) for presence of voltage	
Width	226 mm	
Height	613 mm	
Height	613 mm 706 mm with EMC plate	
Depth	271 mm	
Net Weight	25.5 kg	
Analogue Input Number	3	
, maiogae input irumbei	3	

Al1, Al2, Al3 software-configurable voltage: 010 V DC, impedance: 30 kOhm, resolution 12 bits Al1, Al2, Al3 software-configurable current: 020 mA, impedance: 250 Ohm, resolution 12 bits	
Al2, Al3 software-configurable temperature probe or water level sensor	
6	
DI1DI6 programmable as logic input, 24 V DC (<= 30 V), impedance: 3.5 kOhm DI5, DI6 programmable as pulse input: 030 kHz, 24 V DC (<= 30 V)	
DI1DI6: logic input level 1 PLC conforming to IEC 61131-2 DI5, DI6: pulse input level 1 PLC conforming to IEC 65A-68	
Positive logic (source): DI1DI6 configurable logic input, < 5 V (state 0), > 11 V (state 1)	
Negative logic (sink): DI1DI6 configurable logic input, > 16 V (state 0), < 10 V (state	
1) Positive logic (source): DI5, DI6 configurable pulse input, < 0.6 V (state 0), > 2.5 V (state 1)	
2	
Software-configurable current AQ1, AQ2: 020 mA, resolution 10 bits Software-configurable voltage AQ1, AQ2: 010 V DC impedance 470 Ohm, resolution 10 bits	
5 ms +/- 0.1 ms (Al1, Al2, Al3) - analog input	
2 ms +/- 0.5 ms (DI1DI6)configurable - discrete input 5 ms +/- 1 ms (DI5, DI6)configurable - pulse input	
10 ms +/- 1 ms (AQ1, AQ2) - analog output	
+/- 0.6 % Al1, Al2, Al3 for a temperature variation 60 °C analog input +/- 1 % AQ1, AQ2 for a temperature variation 60 °C analog output	
AI1, AI2, AI3: +/- 0.15 % of maximum value for analog input AQ1, AQ2: +/- 0.2 % for analog output	
3	
Configurable relay logic R1: fault relay NO/NC electrical durability 100000 cycles Configurable relay logic R2: sequence relay NO electrical durability 100000 cycles Configurable relay logic R3: sequence relay NO electrical durability 100000 cycles	
Relay output (R1, R2, R3): 5 ms (+/- 0.5 ms)	
Relay output R1, R2, R3: 5 mA at 24 V DC	
Relay output R1, R2, R3 on resistive load, cos phi = 1: 3 A at 250 V AC Relay output R1, R2, R3 on resistive load, cos phi = 1: 3 A at 30 V DC Relay output R1, R2, R3 on inductive load, cos phi = 0.4 and L/R = 7 ms: 2 A at 250 V AC Relay output R1, R2, R3 on inductive load, cos phi = 0.4 and L/R = 7 ms: 2 A at 30 V DC	
Between power and control terminals	
> 1 MOhm 500 V DC for 1 minute to earth	
75 dB conforming to 86/188/EEC	
842 W(forced convection) at 380 V, switching frequency 4 kHz 109 W(natural convection) at 380 V, switching frequency 4 kHz	
240 m3/h	
240 m3/h Vertical +/- 10 degree	

Vibration Resistance	1.5 mm peak to peak (f= 213 Hz) conforming to IEC 60068-2-6 1 gn (f= 13200 Hz) conforming to IEC 60068-2-6	
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27	
Relative Humidity	595 % without condensation conforming to IEC 60068-2-3	
Ambient Air Temperature For Operation	-1545 °C (without derating) 4560 °C (with derating factor)	
Ambient Air Temperature For Storage	-4070 °C	
Operating Altitude	<= 1000 m without derating 10004800 m with current derating 1 % per 100 m	
Environmental Characteristic	Chemical pollution resistance class 3C3 conforming to IEC 60721-3-3 Dust pollution resistance class 3S3 conforming to IEC 60721-3-3	
Standards	IEC 61800-3 Environment 2 category C3 IEC 61800-3 IEC 61800-5-1 IEC 60721-3	
Marking	CE	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	51.0 cm
Package 1 Width	38.0 cm
Package 1 Length	76.0 cm
Package 1 Weight	29.5 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Resource performance



Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

ATV610D37N4

Dimensions Drawings

Dimensions

IP20 Drives




Drawings from left to right: rear view, right side view with top cover, right side view without top cover.

IP20 Drives With EMC Plate

Product datasheet


ATV610D37N4



Drawings from left to right: rear view, right side view with top cover.

Mounting and Clearance

Clearances




X1	X2	X3
≥ 100 mm (3.94 in.)	≥ 100 mm (3.94 in.)	≥ 10 mm (0.39 in.)

- $_{\bullet}$ Mount the device in a vertical position (±10°). This is required for cooling the device.
- Do not mount the device close to heat sources.
- Leave sufficient free space so that the air required for cooling purposes can circulate from the bottom to the top of the drive.


Mounting Types

Mounting Type A: Individual IP21




a ≥ = 110 mm (4.33 in.)

Mounting Type B: Side by Side IP20 (Possible, 2 Drives Only)



Mounting Type C: Individual IP20


ATV610D37N4



a ≥ = 110 mm (4.33 in.)

Connections and Schema

Single or Three-phase Power Supply - Diagram With Line Contactor



(1) Line chokes


(2) See control block wiring diagram

A1 : Drive

KM1 : Line Contactor Q2, Q3 : Circuit breakers S1, S2 : Pushbuttons

T1: Transformer for control part

Control Block Wiring Diagram




(1) Digital Input (2) Analog Output

(3) Analog Input

R1A, R1B, R1C : Fault relay output R2A, R2C : Sequence relay output R3A, R3C : Sequence relay output

Sensor Connection

It is possible to connect either 1 or 3 sensors on terminals Al2 or Al3.




Product datasheet

ATV610D37N4

Performance Curves

Derating Curves



In: Nominal Drive Current SF: Switching Frequency