# **Product datasheet**

Specification





# variable speed drive ATV610 - 45 kW/60 HP - 380...415 V - IP20

ATV610D45N4

**Training Objectives: Compliant** 

#### Main

IVIAIII			
Range Of Product	Easy Altivar 610		
Product Or Component Type	Variable speed drive		
Product Specific Application	Fan, pump, compressor, conveyor		
Device Short Name	ATV610		
Variant	Standard version		
Product Destination	Asynchronous motors Synchronous motors		
Mounting Mode	Cabinet mount		
Emc Filter	Integrated conforming to IEC 61800-3 category C3 with 50 m		
Ip Degree Of Protection	IP20		
Type Of Cooling	Forced convection		
Supply Frequency	5060 Hz +/-5 %		
Network Number Of Phases	3 phases		
[Us] Rated Supply Voltage	380460 V - 1510 %		
Motor Power Kw	45 kW for normal duty 37 kW for heavy duty		
Motor Power Hp	60 hp for normal duty 50 hp for heavy duty		
Line Current	92.9 A at 380 V (normal duty) 82.7 A at 460 V (normal duty) 80.5 A at 380 V (heavy duty) 69.6 A at 460 V (heavy duty)		
Prospective Line Isc	22 kA		
Apparent Power	65.9 kVA at 460 V (normal duty) 55.4 kVA at 460 V (heavy duty)		
Continuous Output Current	88 A at 4 kHz for normal duty 75 A at 4 kHz for heavy duty		
Maximum Transient Current	97 A during 60 s (normal duty) 112 A during 60 s (heavy duty)		
Asynchronous Motor Control Profile	Optimized torque mode Constant torque standard Variable torque standard		
Output Frequency	0.1500 Hz		
Nominal Switching Frequency	4 kHz		
Switching Frequency	212 kHz adjustable		
Number Of Preset Speeds	16 preset speeds		

Communication Port Protocol	Modbus serial
Option Card	Slot A: communication card, Profibus DP V1 Slot A: digital or analog I/O extension card Slot A: relay output card

# Complementary

Complementary		
Output Voltage	<= power supply voltage	
Motor Slip Compensation	Automatic whatever the load	
	Adjustable	
	Not available in permanent magnet motor law	
	Can be suppressed	
Acceleration And Deceleration	Linear adjustable separately from 0.01 to 9000 s	
Ramps	S, U or customized	
Braking To Standstill	By DC injection	
Protection Type	Thermal protection: motor	
	Motor phase break: motor	
	Thermal protection: drive	
	Overheating: drive	
	Overcurrent between output phases and earth: drive	
	Overload of output voltage: drive	
	Short-circuit protection: drive	
	Motor phase break: drive	
	Overvoltages on the DC bus: drive	
	Line supply overvoltage: drive	
	Line supply undervoltage: drive	
	Line supply phase loss: drive	
	Overspeed: drive	
	Break on the control circuit: drive	
Fraguency Becelution	Pierles with 0.4 Hz	
Frequency Resolution	Display unit: 0.1 Hz	
	Analog input: 0.012/50 Hz	
Electrical Connection	Control, screw terminal: 0.51.5 mm <sup>2</sup>	
	Line side, screw terminal: 3550 mm²	
	Motor, screw terminal: 50 mm <sup>2</sup>	
Connector Type	1 RJ45 (on the remote graphic terminal) for Modbus serial	
Physical Interface	2-wire RS 485 for Modbus serial	
Transmission Frame	RTU for Modbus serial	
Transmission Rate	4.8, 9.6, 19.2, 38.4 kbit/s for Modbus serial	
Type Of Polarization	No impedance for Modbus serial	
Number Of Addresses	1247 for Modbus serial	
Method Of Access	Slave	
Supply	External supply for digital inputs: 24 V DC (1930 V), <1.25 mA, protection type:	
	overload and short-circuit protection	
	Internal supply for reference potentiometer (1 to 10 kOhm): 10.5 V DC +/- 5 %, <10	
	mA, protection type: overload and short-circuit protection	
Local Signalling	2 LEDs for local diagnostic	
	LED (yellow) for embedded communication status	
	2 LEDs (dual colour) for communication module status	
	LED's (dual colour) for communication module status     LED (red) for presence of voltage	
	I LED (160) IOI PIESCITO OI VOILAGE	
Width	226 mm	
Height	613 mm	
	706 mm with EMC plate	
Depth	271 mm	
	Z1 1 11H11	
Net Weight	25.5 kg	
Analogue Input Number	3	

Analogue Input Type	Al1, Al2, Al3 software-configurable voltage: 010 V DC, impedance: 30 kOhm, resolution 12 bits Al1, Al2, Al3 software-configurable current: 020 mA, impedance: 250 Ohm,	
	resolution 12 bits Al2, Al3 software-configurable temperature probe or water level sensor	
Discrete Input Number	6	
Discrete Input Type	DI1DI6 programmable as logic input, 24 V DC (<= 30 V), impedance: 3.5 kOhm DI5, DI6 programmable as pulse input: 030 kHz, 24 V DC (<= 30 V)	
Input Compatibility	DI1DI6: logic input level 1 PLC conforming to IEC 61131-2 DI5, DI6: pulse input level 1 PLC conforming to IEC 65A-68	
Discrete Input Logic	Positive logic (source): DI1DI6 configurable logic input, < 5 V (state 0), > 11 V (state 1)	
	Negative logic (sink): DI1DI6 configurable logic input, > 16 V (state 0), < 10 V (state 1)  Positive logic (source): DI5, DI6 configurable pulse input, < 0.6 V (state 0), > 2.5 V	
 Analogue Output Number	(state 1) 2	
Analogue Output Type	Software-configurable current AQ1, AQ2: 020 mA, resolution 10 bits Software-configurable voltage AQ1, AQ2: 010 V DC impedance 470 Ohm, resolution 10 bits	
Sampling Duration	5 ms +/- 0.1 ms (Al1, Al2, Al3) - analog input	
	2 ms +/- 0.5 ms (DI1DI6)configurable - discrete input 5 ms +/- 1 ms (DI5, DI6)configurable - pulse input	
	10 ms +/- 1 ms (AQ1, AQ2) - analog output	
Accuracy	+/- 0.6 % Al1, Al2, Al3 for a temperature variation 60 °C analog input +/- 1 % AQ1, AQ2 for a temperature variation 60 °C analog output	
Linearity Error	Al1, Al2, Al3: +/- 0.15 % of maximum value for analog input AQ1, AQ2: +/- 0.2 % for analog output	
Relay Output Number	3	
Relay Output Type	Configurable relay logic R1: fault relay NO/NC electrical durability 100000 cycles Configurable relay logic R2: sequence relay NO electrical durability 100000 cycles Configurable relay logic R3: sequence relay NO electrical durability 100000 cycles	
Refresh Time	Relay output (R1, R2, R3): 5 ms (+/- 0.5 ms)	
Minimum Switching Current	Relay output R1, R2, R3: 5 mA at 24 V DC	
Maximum Switching Current	Relay output R1, R2, R3 on resistive load, cos phi = 1: 3 A at 250 V AC Relay output R1, R2, R3 on resistive load, cos phi = 1: 3 A at 30 V DC Relay output R1, R2, R3 on inductive load, cos phi = 0.4 and L/R = 7 ms: 2 A at 250 V AC	
	Relay output R1, R2, R3 on inductive load, cos phi = 0.4 and L/R = 7 ms: 2 A at 30 V DC	
Isolation	Between power and control terminals	
Insulation Resistance	> 1 MOhm 500 V DC for 1 minute to earth	
Environment		
Noise Level	75 dB conforming to 86/188/EEC	
Power Dissipation In W	1000 W(forced convection) at 380 V, switching frequency 4 kHz 121 W(natural convection) at 380 V, switching frequency 4 kHz	
Volume Of Cooling Air	240 m3/h	
Operating Position	Vertical +/- 10 degree	
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 1.2/50 µs - 8/20 µs surge immunity test level 3 conforming to IEC 61000-4-5 Conducted radio-frequency immunity test level 3 conforming to IEC 61000-4-6	
Pollution Degree	2 conforming to IEC 61800-5-1	

Vibration Resistance	1.5 mm peak to peak (f= 213 Hz) conforming to IEC 60068-2-6 1 gn (f= 13200 Hz) conforming to IEC 60068-2-6	
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27	
Relative Humidity	595 % without condensation conforming to IEC 60068-2-3	
Ambient Air Temperature For Operation	-1545 °C (without derating) 4560 °C (with derating factor)	
Ambient Air Temperature For Storage	-4070 °C	
Operating Altitude	<= 1000 m without derating 10004800 m with current derating 1 % per 100 m	
Environmental Characteristic	Chemical pollution resistance class 3C3 conforming to IEC 60721-3-3  Dust pollution resistance class 3S3 conforming to IEC 60721-3-3	
Standards	IEC 61800-3 Environment 2 category C3 IEC 61800-3 IEC 61800-5-1 IEC 60721-3	
Marking	CE	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	34.000 cm
Package 1 Width	52.000 cm
Package 1 Length	73.000 cm
Package 1 Weight	30.200 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Resource performance



#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

#### **Dimensions Drawings**

#### **Dimensions**

#### **IP20 Drives**




Drawings from left to right: rear view, right side view with top cover, right side view without top cover.

#### **IP20 Drives With EMC Plate**

# **Product datasheet**


# ATV610D45N4



Drawings from left to right: rear view, right side view with top cover.

#### Mounting and Clearance

#### Clearances




X1	X2	X3
≥ 100 mm (3.94 in.)	≥ 100 mm (3.94 in.)	≥ 10 mm (0.39 in.)

- $_{\bullet}$  Mount the device in a vertical position (±10°). This is required for cooling the device.
- Do not mount the device close to heat sources.
- Leave sufficient free space so that the air required for cooling purposes can circulate from the bottom to the top of the drive.


#### **Mounting Types**

#### Mounting Type A: Individual IP21




a ≥ = 110 mm (4.33 in.)

#### Mounting Type B: Side by Side IP20 (Possible, 2 Drives Only)



Mounting Type C: Individual IP20


20 May 2024



a ≥ = 110 mm (4.33 in.)

#### Connections and Schema

#### Single or Three-phase Power Supply - Diagram With Line Contactor



(1) Line chokes


(2) See control block wiring diagram

A1 : Drive

KM1 : Line Contactor Q2, Q3 : Circuit breakers S1, S2 : Pushbuttons

T1: Transformer for control part

#### **Control Block Wiring Diagram**




(1) Digital Input (2) Analog Output

(3) Analog Input

R1A, R1B, R1C : Fault relay output R2A, R2C : Sequence relay output R3A, R3C : Sequence relay output

#### **Sensor Connection**

It is possible to connect either 1 or 3 sensors on terminals Al2 or Al3.




# **Product datasheet**

## ATV610D45N4

#### Performance Curves

# **Derating Curves**



In: Nominal Drive Current SF: Switching Frequency