

Lista sa podacima o proizvodima

Specifikacije



stepenasti grebenasti prekidač - 1P
- 60° - 10 A - za Ø 16 ili 22 mm

K10D004NCH

Cena* bez PDV-a: 5.759,00 RSD

Osnovne informacije

Grupa Proizvoda	Harmony K
Tip Proizvoda Ili Komponente	Kompletni grebenasti prekidač
Ime Komponente	K10
[Ith] Dozvoljena Termička Struja U Vazduhu	10 A
Montaža Proizvoda	Prednja ugradnja
Način Pričvršćivanja	Ø 16 ili 22 mm otvor
Tip Glave Grebenastog Prekidača	Sa prednjom pločom 30 x 30 mm
Tip Glave Uređaja	Crna ručica
Zaključavanje Zakretne Ručice	Bez
Natpis	Sa metalik oznakom, 1 - 2 - 3 - 4 crna oznaka
Funkcija Grebenastog Prekidača	Stepenasti grebenasti prekidač
Povratak	Bez
Off Položaj	Bez Off pozicije
Broj Polova	1P
Pozicije Prekidača	Desno: 270° - 330° - 30° - 90°
Ip Stepen Zaštite	Kontaktni blok: IP20 Glava: IP65 conforming to IEC 60529

Dopunske informacije

Broj Koraka	4
Ugao Grebenastog Prekidača	60 °
[Ui] Nazivni Napon Izolacije	440 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
Nazivna Snaga U W	370 W AC-23A, 110/120 V monofazne 750 W AC-23A, 220/240 V monofazne
Nazivna Snaga U Hp	0,33 hp pri 110/120 V AC, monofazne 0,75 hp pri 220/240 V AC, monofazne
[Ie] Nazivna Struja Ac	10 A pri 400 V AC-1 10 A pri 400 V AC-21A 3 A pri 240 V AC-15 6 A pri 120 V AC-15
[Ie] Nazivna Struja Dc	10 A pri 24 V rezistivno opterećenje 0,3 A pri 220 V rezistivno opterećenje 0,7 A pri 110 V rezistivno opterećenje
Električna Trajnost	100000000 ciklusa

Zaštita Od Kratkog Spoja 10 A rastavni uložak osigurač, tip gG
Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

[Uimp] Nazivni Podnosivi Impulsni Napon	4 kV u skladu sa IEC 60947-1
Operacija Kontakata	Sporo isključenje
Električna Veza	Neodvojivi vijčani priključni blokovi, kapacitet stezaljke: 2 x 1.5 mm²
Mehanička Trajnost	1000000 ciklusa
Cad Ukupna Širina	30 mm
Cad Ukupna Visina	30 mm
Cad Ukupna Dubina	88 mm
Masa Proizvoda	0,045 kg

Okruženje

Standardi	CENELEC EN 50013 EN/IEC 60947-3 EN/IEC 60947-5-1
Sertifikacije Proizvoda	CULus
Tretman Zaštite	TC
Temperatura Okoline Za Rad Uređaja	-20...55 °C
Temperatura Okoline Za Skladištenje	-40...70 °C
Klasa Zaštite Protiv Električnog Udara	Klasa II u skladu sa IEC 60536

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10,5 cm
Package 1 Width	4,1 cm
Package 1 Length	4,0 cm
Package 1 Weight	67,0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	65
Package 2 Height	15,0 cm
Package 2 Width	30,0 cm
Package 2 Length	40,0 cm
Package 2 Weight	4,665 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)


Performanse dobrobiti

	Reach Bez Svhc	
	Bez Toksičnih Teških Metala	
	Bez Žive	
	Informacije O Rohs Izuzecima	Da
Propis Reach		REACH deklaracija
Eu Rohs Direktiva		Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Rohs Regulatorna Za Kinu		RoHS deklaracija za Kinu
Weee		Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Dimensions Drawings

Cam Switch

Front Mounting by Ø16 mm/0.63 in. or Ø 22 mm/0.87 in. hole




- a 63 mm/2.48 in.
- e support panel thickness: 0.5 mm to 5 mm/0.02 in. to 0.2 in.

Mounting and Clearance


Cam Switch

Ø 16 mm/0.63 in. and Ø 22 mm/0.87 in. Panel Cut-outs




Technical Description


Link Positions (Factory Mounted)




Marking



Angular Position of Switch



Switching Program



Convention Used for Switching Program Representation

- Contact closed
- Contact closed in 2 positions and maintained between the 2 positions
- Sealed assembly for auto-maintain control
- Overlapping contacts
- Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

