

Lista sa podacima o proizvodima

Specifikacije



ampermetarski grebenasti
prekidač - 3 kola - 90° - 12 A -
vijčana montaža

K1F003MLH

Cena* bez PDV-a: 2.905,00 RSD

Osnovne informacije

Grupa Proizvoda	Harmony K
Tip Proizvoda Ili Komponente	Kompletni grebenasti prekidač
Ime Komponente	K1
[Ith] Dozvoljena Termička Struja U Vazduhu	12 A
Montaža Proizvoda	Prednja ugradnja
Način Pričvršćivanja	Na više načina
Tip Glave Grebenastog Prekidača	Sa prednjom pločom 45 x 45 mm
Tip Glave Uređaja	Crna ručica, dužina = 35 mm
Zaključavanje Zakretne Ručice	Bez
Natpis	Sa metalik oznakom, 0 - L1 - L2 - L3 crna oznaka
Funkcija Grebenastog Prekidača	Ampermetarski grebenasti prekidač
Povratak	Bez
Tip Merenja	Za 3 kola
Off Položaj	Sa Off pozicijom
Pozicije Prekidača	Desno: 0° - 90° - 180° - 270°
Ip Stepen Zaštite	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010

Dopunske informacije

Ugao Grebenastog Prekidača	90 °
[Ui] Nazivni Napon Izolacije	690 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
[Ithe] Dozvoljena Termička Struja U Ormanu	10 A
Nazivna Snaga U W	10500 W AC-21, 500...660 V trofazne u skladu sa IEC 60947-3 1100 W AC-3, 230 V trofazne u skladu sa IEC 60947-3 1500 W AC-23A, 230 V trofazne u skladu sa IEC 60947-3 1500 W AC-3, 400 V monofazne u skladu sa IEC 60947-3 1500 W AC-3, 400 V trofazne u skladu sa IEC 60947-3 1500 W AC-3, 500 V trofazne u skladu sa IEC 60947-3 1500 W AC-3, 690 V trofazne u skladu sa IEC 60947-3 2200 W AC-23A, 400 V trofazne u skladu sa IEC 60947-3 2200 W AC-23A, 500 V trofazne u skladu sa IEC 60947-3 2200 W AC-23A, 690 V trofazne u skladu sa IEC 60947-3 4800 W AC-21, 230 V trofazne u skladu sa IEC 60947-3 600 W AC-3, 230 V monofazne u skladu sa IEC 60947-3 8300 W AC-21, 400 V trofazne u skladu sa IEC 60947-3

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

[Ie] Nazivna Struja Ac	1 A pri 500 V AC-15 u skladu sa IEC 60947-5-1 2 A pri 400 V AC-15 u skladu sa IEC 60947-5-1 3 A pri 230 V AC-15 u skladu sa IEC 60947-5-1 1,8 A pri 690 V AC-3 trofazne u skladu sa IEC 60947-3 2,8 A pri 500 V AC-3 trofazne u skladu sa IEC 60947-3 2,8 A pri 690 V AC-23A trofazne u skladu sa IEC 60947-3 3,3 A pri 400 V AC-3 trofazne u skladu sa IEC 60947-3 3,8 A pri 500 V AC-23A trofazne u skladu sa IEC 60947-3 4,6 A pri 230 V AC-3 trofazne u skladu sa IEC 60947-3 4,8 A pri 400 V AC-23A trofazne u skladu sa IEC 60947-3 5,6 A pri 230 V AC-23A trofazne u skladu sa IEC 60947-3
Električna Trajnost	1000000 ciklusa AC-15 1000000 ciklusa AC-21 500000 ciklusa AC-23 500000 ciklusa AC-3
Maksimalni Radni Ciklus	2,5 ciklusa/min AC-21 2,5 ciklusa/min AC-23 2,5 ciklusa/min AC-3 8,333 ciklusa/min AC-15
Struja Kratkog Spoja	10000 A
Zaštita Od Kratkog Spoja	16 A rastavni uložak osigurač, tip gG
[Uimp] Nazivni Podnosivi Impulsni Napon	4 kV u funkciji izolacije 6 kV u skladu sa IEC 60947-1
Operacija Kontakata	Sporo isključenje
Pozitivno Otvaranje	Sa
Električna Veza	Neodvojivi vijčani priključni blokovi fleksibilni, kapacitet stezaljke: 2 x 1.5 mm² Neodvojivi vijčani priključni blokovi jednožični, kapacitet stezaljke: 1 x 2.5 mm²
Mehanička Trajnost	1000000 ciklusa
Cad Ukupna Širina	45 mm
Cad Ukupna Visina	45 mm
Cad Ukupna Dubina	97 mm
Masa Proizvoda	0,17 kg

Okruženje

Standardi	CENELEC EN 50013 EN/IEC 60947-3 za kolo napajanja EN/IEC 60947-5-1 za upravljačko kolo
Sertifikacije Proizvoda	CSA 240 V 1 hp monofazne CSA 240 V 3 hp trofazne 2 polni UL 240 V 1 hp trofazne UL 240 V 0,33 hp monofazne 2 polni
Tretman Zaštite	TC
Temperatura Okoline Za Rad Uređaja	-25...55 °C
Temperatura Okoline Za Skladištenje	-40...70 °C
Otpornost Na Udare	30 gn u skladu sa IEC 68-2-27
Otpornost Na Vibracije	5 gn (f = 10...150 Hz) u skladu sa IEC 68-2-6
Klasa Zaštite Protiv Električnog Udara	Klasa II u skladu sa IEC 536 Klasa II u skladu sa NF C 20-030

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6,600 cm

Package 1 Width	6,600 cm
Package 1 Length	11,200 cm
Package 1 Weight	180,000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	40
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7,655 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	70,820 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti


✓	Reach Bez Svhc	
✓	Bez Toksičnih Teških Metala	
✓	Bez Žive	
✓	Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Operating Head and Body


Front Mounting "Multi-Fixing"




- a 73 mm/2.87 in.
- e support panel thickness 1 mm to 6 mm./0.039 in. to 0.24 in.

Technical Description


Link Positions (Factory Mounted)




Marking



Angular Position of Switch



Switching Program



Convention Used for Switching Program Representation

-  Contact closed
-  Contact closed in 2 positions and maintained between the 2 positions
-  Sealed assembly for auto-maintain control
-  Overlapping contacts
-  Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

