# **Product datasheet**

Specifications





# circuit breaker Compact NSX250F DC - 250 A - 4 poles - fixed without trip unit

LV438208

() Discontinued on: 15 Jun 2023

① Discontinued

#### Main

mann		
Range	ComPact	
Range Of Product	ComPact NSX100250 DC	
Device Short Name	NSX250F DC	
Product Or Component Type	Basic frame	
Device Application	Distribution	
Circuit Breaker Name	Compact NSX250F DC	
Number Of Poles	4P	
[In] Rated Current	250 A at 40 °C	
[Ue] Rated Operational Voltage	750 V DC	
Network Type	DC	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Utilisation Category	Category A	
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	36 kA Icu at 250 V DC 1P conforming to IEC 60947-2 36 kA Icu at 24125 V DC 1P conforming to IEC 60947-2 36 kA Icu at 500 V DC 2P conforming to IEC 60947-2 36 kA Icu at 750 V DC 3P conforming to IEC 60947-2	
Performance Level	F 36 kA 750 V DC	
Control Type	Toggle	
Mounting Mode	Fixed	

#### Complementary

[Ui] Rated Insulation Voltage	750 V DC conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	36 kA at 250 V DC conforming to IEC 60947-2 (1P) 36 kA at 48/125 V DC conforming to IEC 60947-2 (1P) 36 kA at 500 V DC conforming to IEC 60947-2 (2P) 36 kA at 750 V DC conforming to IEC 60947-2 (3P)
Maximum Breaking Time	10 ms
Mechanical Durability	10000 cycles conforming to IEC 60947-2
Electrical Durability	10000 cycles 250 V DC In/2 conforming to IEC 60947-2 10000 cycles 500 V DC In/2 conforming to IEC 60947-2 10000 cycles 750 V DC In/2 conforming to IEC 60947-2 5000 cycles 250 V DC In conforming to IEC 60947-2 5000 cycles 500 V DC In conforming to IEC 60947-2 5000 cycles 750 V DC In conforming to IEC 60947-2

Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	Without protection
Width (W)	140 mm
Height (H)	161 mm
Depth (D)	86 mm

## Environment

Standards	IEC 60947-2
Product Certifications	ASTA ASEFA KEMA LCIE
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	14.3 cm
Package 1 Length	18.8 cm
Package 1 Weight	2.138 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information