



TeSys Vario - switch disconnector - 12 A - on door

VBF02

! Discontinued on: 22 Jul 2020

! Discontinued

Main

Range	TeSys	
Product Name	TeSys VARIO	
Device Short Name	VBF	
Device Application	Preventive maintenance	
Product Type	Switch disconnector	

Complementary

Device Composition	Switch Handle
Mounting Support	Handle: door Switch: door
Mounting Method	By 4 screws for handle
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
[Ue] lec Rated Operational Voltage	690 V AC 50/60 Hz
lec Rated Operational Power In W	3 kW at 400415 V (AC-3) 4 kW at 500 V (AC-3) 1.5 kW at 230240 V (AC-3) 5.5 kW at 500 V (AC-23A) 5.5 kW at 690 V (AC-3) 7.5 kW at 690 V (AC-23A) 3 kW at 230240 V (AC-23A) 4 kW at 400415 V (AC-23A)
[le] Rated Operational Current	8.1 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	12 A
[Ithe] Conventional Enclosed Thermal Current	10 A
Making Capacity (I Rms)	120 A at 400 V AC-21A 120 A at 400 V AC-22A 120 A at 400 V AC-23A
Breaking Capacity	120 A at 400 V (AC-21A) 120 A at 400 V (AC-22A) 120 A at 400 V (AC-23A)
Rated Conditional Short Circuit Current	10 kA at 400 V - associated fuse 12 A aM 10 kA at 400 V - associated fuse 12 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA at 400 V at Ipeak

[Icw] Rated Short Time Withstand Current	300 A at 400 V duration: 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV
Suitability For Isolation	Yes
Network Type	DC AC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct
Handle Color	Black
Handle Front Plate Color	Black
Rotary Handle Padlocking	1 to 3 padlocks 48 mm
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-1 30000 cycles DC-2 30000 cycles DC-3 30000 cycles DC-4 30000 cycles DC-5
lec Terminal Connection	Power circuit: screw clamp terminals10 mm² - solid Power circuit: screw clamp terminals6 mm² - flexible - with cable end
Tightening Torque	Power circuit: 2.1 N.m - on screw clamp terminals
Base Dimension	60 x 60 mm
Height	74 mm
Width	60 mm
Product Weight	0.25 kg

Environment

Standards	IEC 60947-3
Product Certifications	GL
	UL
	CSA
	CCC
	UKCA
Degree Of Protection	IP20 conforming to IEC 60529
	IP65
Protective Treatment	TC
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6
	Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-2050 °C
···	000 00
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	Main switch disconnector

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm

Package 1 Width	8.400 cm
Package 1 Length	12.000 cm
Package 1 Weight	219.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.730 kg

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free
②	Mercury Free
⊘	Rohs Exemption Information Yes
②	Pvc Free
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

19 Apr 2024