

Product datasheet

Specifications



Complete joystick controller, Harmony XK, XKBA light hosting application

XKBA14330

⚠ Discontinued on: 31 Oct 2022

⚠ Discontinued

Main

Range Of Product	Harmony XK
Product Or Component Type	Complete joystick controller
Product Specific Application	Light hoisting applications

Complementary

Device Short Name	XKB
Bezel Material	Metal
Fixing Collar Material	Metal
Sale Per Indivisible Quantity	1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-20...70 °C
Overvoltage Category	Class I conforming to IEC 61140
Ip Degree Of Protection	IP54 conforming to IEC 60529
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508
Product Certifications	CSA UL CCC RRS
Contact Code Designation	Q300 A300
Operator Position Information	All positions
Operator Profile	Standard handle
Notch Per Direction	1...3 notches at 12°-20°-28° for each direction
Mechanical Durability	1000000 cycles
Vibration Resistance	6 gn (f= 1...70 Hz) conforming to IEC 60068-2-6
Shock Resistance	20 gn (duration = 11 ms) conforming to IEC 60068-2-6
Connections - Terminals	Captive screw clamp terminals, <= 2 x 1.5 mm² with cable end Captive screw clamp terminals, <= 1 x 2.5 mm² without cable end Captive screw clamp terminals, >= 1 x 0.5 mm²
Short-Circuit Protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ith] Conventional Free Air Thermal Current	10 A conforming to EN/IEC 60947-5-1 10 A conforming to CSA C22.2 No 14 10 A conforming to UL 508
[Ui] Rated Insulation Voltage	500 V (pollution degree 3) conforming to IEC 60947-1
Compatibility Code	XKB

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.0 cm
Package 1 Width	16.5 cm
Package 1 Length	24.0 cm
Package 1 Weight	453.592 g

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration