

# Product datasheet

Specifications



Acti9 - MIN - electromechanical timer - adjustable from 1 to 7 minutes

15363

Price: 63,831.82 NGN

## Main

Range Of Product	Acti9
Product Name	Acti9 MIN
Device Short Name	MIN
Product Or Component Type	Electromechanical timer
Colour Tint	White (RAL 9003)

## Complementary

Device Application	Building
Load Type	Parallel-corrected fluorescent tube 14 x 40 W 4.7 µF Parallel-corrected fluorescent tube 10 x 58 W 7 µF Parallel-corrected fluorescent tube 3.0 x 100 W 18 µF 230 V AC halogen lamp 2300 W 230 V AC incandescent lamp 2300 W Fluocompact lamp 2300 VA Compact fluorescent lamp 21 x 7 W Compact fluorescent lamp 13 x 11 W Compact fluorescent lamp 10 x 15 W Compact fluorescent lamp 7 x 20 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Power Consumption In Va	1 VA
Maximum Switching Current	16 A - 230 V AC pf = 1
[Ue] Rated Operational Voltage	230 V AC at 50 Hz
Time Delay	Adjustable from 1 to 7 minutes
Mounting Support	DIN rail
9 Mm Pitches	2
Connections - Terminals	Screw terminals - <= 6 mm²
Width	18 mm
Height	83 mm
Depth	68 mm
Net Weight	84 g

## Environment

Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	IP20 B

## Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7 cm
Package 1 Length	9.9 cm
Package 1 Weight	82 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.5 cm
Package 2 Width	10.5 cm
Package 2 Length	22 cm
Package 2 Weight	865 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	110
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	10.033 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>