

Product datasheet

Specifications



InRow RC, 300mm, Chilled Water, 200-240V, 50/60 Hz

ACRC103

⚠ Discontinued on: 1 Apr 2016

⚠ To be end-of-service on: 31 Mar 2026

⚠ Discontinued - Service only

Overview

Lead Time While Supplies Last

Main

Input Connection Type	IEC 60309 16 A 2P + E
Number Of Rack Unit	42U
Number Of Cables	2
Provided Equipment	Installation guide Operations and maintenance manual

General

Air Discharge Option	Horizontal
Intake Air Option	Rear return
Air Flow	1368.65 l/s
Minimum Water Inlet Temperature	7 °C
Condensate Pump Flow	0.00 m3/h

Physical

Colour	Black
Height	199.1 cm
Width	30 cm
Depth	107 cm
Net Weight	162.73 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Power	1000 W
Network Frequency	50/60 Hz

Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	C-Tick CE GOST MEA VDE
Standards	EN 55022 class A EN 55024 EN 60950 IEC 60950 IEC 61000-3-2 IEC 61000-3-3

Communications & Management

Control Panel	Multifunction LCD status and control console
---------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	211.8 cm
Package 1 Width	113.7 cm
Package 1 Length	74.6 cm
Package 1 Weight	193.41 kg
Number Of Units In Package 3	1

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
