Product datasheet

Specifications



Full-flat switch with Ondicator, ZENcole, 16AX/20A, 2 gang, 1 way, silver bronze

E8432_1_SZ

Price: 12,511.36 NGN

Main

Range	ZENcelo	
Product Or Component Type	Switch	
Load Type	Fluorescent lamp Resistive Inductive Incandescent lamp	
Colour Tint	Silver bronze	
Cover Frame Colour Tint	t Silver bronze	

Complementary

Device Mounting	Flush Surface	
Switch Function	1-way	
Rated Current	16 AX at 250 V AC 50/60 Hz 20 A	
Local Signalling	Mechanical indicator (amber)	
Number Of Gangs	er Of Gangs 2 gangs	
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround	
Connections - Terminals	Brass rod terminals	
Width	87 mm	
Height	87 mm	
Depth	31 mm	

Environment

Ambient Air Temperature For Operation	-535 °C	
Relative Humidity	095 %	
Environmental Characteristic	No UV resistant	
Operating Altitude	2000 m	
Standards	MS IEC 60669-1 IEC 60669-1 GB 16915.1 SS 227-1 BS EN 60669-1	

Packing Units

1

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	112.42 g

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations