

Lista sa podacima o proizvodima

Specifikacije



SERCOS III field bus interfejs modul

TM5NS31

Cena* bez PDV-a: 28.696,93 RSD

Osnovne informacije

Grupa Proizvoda	Modicon TM5
Tip Proizvoda Ili Komponente	Sercos III komunikacioni modul
Fizički Interfejs	EcoStruxure EV Charging Expert

Dopunske informacije

Kompatibilnost Grupe Proizvoda	Modicon LMC078
Kompatibilnost Proizvoda	Servo kontroler
Integrisani Načini Povezivanja	Ethernet/IP, 2 RJ45 konektora Sercos, 100 Mbit/s
Potrošnja Struje	350 mA pri 5 V DC, baza
Sastav Uređaja	Interfejs modul Bus baza poručiti zasebno Napajanje poručiti zasebno Priključni blok poručiti zasebno
Maksimalna Snaga Disipacije U W	1,75 W
Boja	Bela
Lokalna Signalizacija	1 LED zelena/crvena za STAT 1 LED zelena/crvena za Sercos III 1 LED zelena za Sercos III port 1 1 LED zelena za Sercos III port 2
Masa Proizvoda	0,03 kg

Okruženje

Otpornost Na Elektrostatičko Praznjenje	4 kV na kontaktu u skladu sa IEC 61000-4-2 8 kV u vazduhu u skladu sa IEC 61000-4-2
Otpornost Na Elektromagnetna Polja	1 V/m 2...2.7 GHz u skladu sa IEC 61000-4-3 10 V/m 80 MHz...2 GHz u skladu sa IEC 61000-4-3
Otpornost Na Brze Prelaze	1 kV u skladu sa IEC 61000-4-4 (I/O) 1 kV u skladu sa IEC 61000-4-4 (oklopljen kabl) 2 kV u skladu sa IEC 61000-4-4 (napojni vod)
Podnosivi Naponski Udar	0,5 kV diferencijalni mod u skladu sa IEC 61000-4-5 1 kV asimetrični napon u skladu sa IEC 61000-4-5
Elektromagnetna Kompatibilnost	EN/IEC 61000-4-6
Smetnje Emisije Vezane Sa Vodovima I Zračenjem	CISPR 11

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Package 1 Height	3,000 cm
Package 1 Width	6,000 cm
Package 1 Length	10,500 cm
Package 1 Weight	72,000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	3,852 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

- ✓

Bez Toksičnih Teških Metala
- ✓

Bez Žive
- ✓

Informacije O Rohs Izuzecima

Da
- ✓

Bez Pvc


Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka

Presentation

Presentation

Sercos fieldbus interface module




- 1 Locking clip
- 2 Status LEDs
- 3 Sercos III address setting rotary switches
- 4 Sercos III Port 1 connector (RJ45)
- 5 Sercos III Port 2 connector (RJ45)

Dimensions Drawings

Dimensions and Schema

Sercos Fieldbus Interface Module


Dimensions




Mounting and Clearance

TM5 System


Spacing Requirements



Mounting Position




Mounting on a Din Rail



Connections and Schema

Wiring Diagram



- (A) Interface Power Distribution Module (IPDM)
- (1) Internal electronics
- (2) 24 Vdc I/O power segment integrated in the bus bases
- (3) PS1/PS2: External isolated power supply 24 Vdc
- (4) External fuse, Type T slow blow, 10 A max., 250 V
- (5) External fuse, Type T slow blow, 1 A, 250 V