

Lista sa podacima o proizvodima

Specifikacije



narandžasta kompl. signalna
lampica Ø22 ravna sočiva sa BA9s
sijalicom 220..240V

XB4BV45

Cena* bez PDV-a: 4.084,63 RSD

Osnovne informacije

Grupa Proizvoda	Harmony XB4
Tip Proizvoda Ili Komponente	Lampica
Kratko Ime Uređaja	XB4
Materijal Podnožja	Hromirani metal
Materijal Montažnog Rama	Zamak
Tip Glave	Standardni
Prečnik Za Montiranje	22,5 mm
Prodaja Po Nedeljivim Količinama	1
Oblik Glave Signalne Jedinice	Okrugla
Boja Kapica/Glave Ili Sočiva	Narandžasta
Dodatne Informacije O Glavi Uređaja	Sa glatkim sočivima
Svetlosni Izvor	Inkandescentna
Baza Sijalice	BA 9s
Napajanje Svetlosnog Bloka	Putem integrisanog transformatora 1,2 VA 6 V
[Us] Nazivni Napon	230...240 V AC pri 50/60 Hz

Dopunske informacije

Visina	47 mm
Širina	30 mm
Dubina	78 mm
Opis Priključaka Iso N°1	(X1-X2)PL
Masa Proizvoda	0,152 kg
Otpornost Na Uređaj Za Pranje Pod Pritiskom	7000000 Pa pri 55 °C, razdaljina : 0.1 m
Povezivanje - Priklučci	Vijčani priključni blokovi, <= 2 x 1.5 mm² sa kablovskim završetkom u skladu sa IEC 60947-1 Vijčani priključni blokovi, 1 x 0.22...2 x 2.5 mm² bez kablovskog završetka u skladu sa IEC 60947-1
[Ui] Nazivni Napon Izolacije	600 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
[Uimp] Nazivni Podnosivi Impulsni Napon	6 kV u skladu sa IEC 60947-1
Tip Signalizacije	Trajna
Prezentacija Uređaja	Kompletan proizvod

Okruženje

Sve informacije navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Tretman Zaštite	TH
Temperatura Okoline Za Skladištenje	-40...70 °C
Temperatura Okoline Za Rad Uređaja	-40...55 °C
Klasa Zaštite Protiv Električnog Udara	Klasa I u skladu sa IEC 60536
Ip Stepen Zaštite	IP66 u skladu sa IEC 60529 IP67 IP69 IP69K
Nema Stepen Zaštite	NEMA 13 NEMA 4X
Ik Stepen Zaštite	IK06 conforming to IEC 50102
Standardi	IEC 60947-1 IEC 60947-5-5 IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-4 UL 508 JIS C8201-5-1 JIS C8201-1
Sertifikacija Proizvoda	UL odobrenje CSA
Otpornost Na Vibracije	5 gn (f= 12...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	30 gn (trajanje = 18 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27 50 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8,4 cm
Package 1 Width	4,8 cm
Package 1 Length	3,4 cm
Package 1 Weight	146,0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8,8 cm
Package 2 Width	26,5 cm
Package 2 Length	3,4 cm
Package 2 Weight	735,0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	50
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	7,788 kg

Ugovorna garancija

Garancija

18 meseci

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

✓ Bez Žive	
✓ Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi


Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka

Lista sa podacima o
proizvodima

XB4BV45

Dimensions Drawings

Dimensions





e : clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

a in mm	a in in.	b in mm	b in in.	c in mm	c in in.
66	2.60	30	1.18	46.5	1.83

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board	Connection by Faston Connectors
	
(1) Diameter on finished panel or support (2) 40 mm min. / 1.57 in. min. (3) 30 mm min. / 1.18 in. min. (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $^{+0.4}_0$ / 0.88 in. $^{+0.016}_0$) (5) 45 mm min. / 1.78 in. min. (6) 32 mm min. / 1.26 in. min.	