

Lista sa podacima o proizvodima

Specifikacije



zelena kompletna signalna
lampica Ø22 ravna sočiva sa
integrisanim LED 400V

XB5AV5B3

Osnovne informacije

Grupa Proizvoda	Harmony XB5
Tip Proizvoda Ili Komponente	Lampica
Kratko Ime Uređaja	XB5
Materijal Podnožja	Tamno siva plastika
Materijal Montažnog Rama	Plastika
Tip Glave	Standardni
Prečnik Za Montiranje	22,5 mm
Prodaja Po Nedeljivim Količinama	1
Oblik Glave Signalne Jedinice	Okrugla
Boja Kapica/Glave Ili Sočiva	Zelena
Dodatne Informacije O Glavi Uređaja	Sa glatkim sočivima
Svetlosni Izvor	Universal LED
Baza Sijalice	Integrisan LED
Boja Svetlosnog Izvora	Zelena
[Us] Nazivni Napon	400 V AC pri 50 Hz
Prezentacija Uređaja	Kompletan proizvod

Dopunske informacije

Cad Ukupna Širina	40 mm
Cad Ukupna Visina	45 mm
Cad Ukupna Dubina	101 mm
Masa Proizvoda	0,133 kg
Otpornost Na Uređaj Za Pranje Pod Pritiskom	7000000 Pa pri 55 °C, razdaljina : 0.1 m
Povezivanje - Priključci	Vijčani priključni blokovi, <= 2 x 1.5 mm² sa kablovskim završetkom u skladu sa IEC 60947-1
[Ui] Nazivni Napon Izolacije	600 V (stepen zaprljanosti 3) u skladu sa IEC 60947-1
Tip Signalizacije	Trajna
Granice Napona	407...423 V AC
Servisni Vek	100000 sati pri nazivnom naponu i 25 °C
Podnosivi Naponski Udar	1 kV u skladu sa IEC 61000-4-5

Okruženje

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Tretman Zaštite	TH
Temperatura Okoline Za Skladištenje	-40...70 °C
Temperatura Okoline Za Rad Uređaja	-40...70 °C
Klasa Zaštite Protiv Električnog Udara	Klasa II u skladu sa IEC 60536
Ip Stepen Zaštite	IP66 u skladu sa IEC 60529 IP67 u skladu sa IEC 60529 IP69 u skladu sa IEC 60529 IP69K u skladu sa ISO 20653
Nema Stepen Zaštite	NEMA 13 NEMA 4X
Ik Stepen Zaštite	IK05 conforming to IEC 50102
Standardi	CSA C22.2 No 14 UL 508 IEC 60947-5-4 IEC 60947-1 JIS C8201-5-1 IEC 60947-5-1 JIS C8201-1
Sertifikacija Proizvoda	UL odobrenje CSA
Otpornost Na Vibracije	2 gn (f= 12...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	15 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27
Otpornost Na Brze Prelaze	2 kV u skladu sa IEC 61000-4-4
Otpornost Na Elektromagnetna Polja	10 V/m u skladu sa IEC 61000-4-3
Otpornost Na Elektrostatičko Pražnjenje	6 kV na kontaktu (metalnim delovima) u skladu sa IEC 61000-4-2 8 kV u vazduhu (u izolovanim delovima) u skladu sa IEC 61000-4-2
Elektromagnetna Emisija	Klasa B u skladu sa IEC 55011

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11,9 cm
Package 1 Width	5,2 cm
Package 1 Length	4,4 cm
Package 1 Weight	133 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7,105 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH


Performanse dobrobiti

✓ Bez Žive	
✓ Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulatorna Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka

Dimensions



- e: clamping thickness: 1 mm to 6 mm / 0.04 in. to 0.24 in.
a: 89.6 mm / 3.53 in.
b: 40 mm / 1.57 in.
c: 45 mm / 1.77 in.

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
(3) Ø22.5 mm recommended ($\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$) / Ø0.89 in. recommended ($\text{Ø}0.88 \text{ in.} \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- (1) Diameter on finished panel or support
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
(3) Ø22.5 mm recommended ($\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$) / Ø0.89 in. recommended ($\text{Ø}0.88 \text{ in.} \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$)