Product data sheet

Specification





Head for pilot light, Harmony 9001K, metal, without cap, 30mm, 110...120V

9001KP1

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Head for pilot light	
Device Short Name	К	

Complementary

Bezel Material	Metal
Mounting Diameter	30 mm
Cap/Operator Or Lens Colour	Without cap
Bulb Base	BA 9s
Light Block Supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz
Shape Of Screw Head	Round
Light Source	Incandescent bulb
Operating Mode	Normal
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Supply Frequency	5060 Hz
Size	30 mm

Environment

Product Certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.572 cm
Package 1 Width	5.588 cm
Package 1 Length	9.144 cm
Package 1 Weight	222.26 g
Unit Type Of Package 2	PAL

Number Of Units In Package 2	1200
Package 2 Height	101.6 cm
Package 2 Width	101.6 cm
Package 2 Length	121.92 cm
Package 2 Weight	272.609 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations