# **Product data sheet**

Specifications





# TeSys Deca contactor , 3P(3 NO) , AC-3 , <= 440V, 50 A , 500V AC 50/60 Hz coil

LC1D50AS7

! Discontinued on: 8/12/2020

(!) Discontinued

#### Main

<u> </u>		
Range	TeSys	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-3 AC-4 AC-1	
Poles Description	3P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] Rated Operational Current	50 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
[Uc] Control Circuit Voltage	500 V AC 50/60 Hz	

#### Complementary

Motor Power Kw	15 kW at 220230 V AC 50/60 Hz (AC-3)	
	22 kW at 380400 V AC 50/60 Hz (AC-3)	
	30 kW at 500 V AC 50/60 Hz (AC-3)	
	33 kW at 660690 V AC 50/60 Hz (AC-3)	
	25 kW at 415 V AC 50/60 Hz (AC-3)	
	30 kW at 440 V AC 50/60 Hz (AC-3)	
	11 kW at 400 V AC 50/60 Hz (AC-4)	
Motor Power Hp	3 hp at 115 V AC 50/60 Hz for 1 phase motors	
	7.5 hp at 230/240 V AC 50/60 Hz for 1 phase motors	
	15 hp at 200/208 V AC 50/60 Hz for 3 phases motors	
	15 hp at 230/240 V AC 50/60 Hz for 3 phases motors	
	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors	
	40 hp at 575/600 V AC 50/60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Contact Compatibility	M2	
Protective Cover	With	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	80 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	900 A at 440 V for power circuit conforming to IEC 60947	

24/04/2024 Life Is On Schneider

Rated Breaking Capacity	900 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	400 A 40 °C - 10 s for power circuit
Current	810 A 40 °C - 1 s for power circuit
	84 A 40 °C - 10 min for power circuit
	208 A 40 °C - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	100 A gG at <= 690 V coordination type 1 for power circuit
	100 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	3.7 W AC-3
	9.6 W AC-1
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
	Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.45 Mcycles 50 A AC-3 at Ue <= 440 V 1.1 Mcycles 80 A AC-1 at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz
Constant Voltage Limits	
	0.81.1 Uc (-4060 °C):operational AC 50 Hz
	0.851.1 Uc (-4060 °C):operational AC 60 Hz
	11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C)
	160 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening
	1226 ms closing
Maximum Operating Poto	3600 availe 60 °C
Maximum Operating Rate	3600 cyc/h 60 °C

cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible
Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
without cable end Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible without cable end
with cable end  Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible
with cable end  Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: solid
without cable end
Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: solid without cable end
Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver flat Ø
6 mm Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver
Philips No 2 Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm²
hexagonal screw head 4 mm
Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm <sup>2</sup> hexagonal screw head 4 mm
1 NO + 1 NC
type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
25400 Hz
17 V for signalling circuit
5 mA for signalling circuit
> 10 MOhm for signalling circuit
1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Plate Rail
CSA C22.2 No 14
EN 60947-4-1 EN 60947-5-1
IEC 60947-4-1
IEC 60947-5-1 UL 508
BV
GOST DNV
LROS (Lloyds register of shipping)
CCC RINA
CSA
GL UL
IP20 front face conforming to IEC 60529
·

Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (10 Gn for 11 ms)
Height	122 mm
Width	55 mm
Depth	120 mm
Net Weight	0.855 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	14 cm
Package 1 Length	15 cm
Package 1 Weight	850 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information