Product data sheet

Specification





Contactor, TeSys Deca, 3P(3 NO), AC-3/AC-3e, <=400V, 50A, 480V AC 60Hz coil, screw clamp terminals

LC1D50AT7

Main

Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	50 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 50 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	480 V AC 60 Hz

Complementary

Motor Power Kw	15 kW at 220230 V AC 50/60 Hz (AC-3)
	22 kW at 380400 V AC 50/60 Hz (AC-3)
	30 kW at 500 V AC 50/60 Hz (AC-3)
	33 kW at 660690 V AC 50/60 Hz (AC-3)
	25 kW at 415 V AC 50/60 Hz (AC-3)
	30 kW at 440 V AC 50/60 Hz (AC-3)
	11 kW at 400 V AC 50/60 Hz (AC-4)
	15 kW at 220230 V AC 50/60 Hz (AC-3e)
	22 kW at 380400 V AC 50/60 Hz (AC-3e)
	30 kW at 500 V AC 50/60 Hz (AC-3e)
	33 kW at 660690 V AC 50/60 Hz (AC-3e)
	25 kW at 415 V AC 50/60 Hz (AC-3e)
	30 kW at 440 V AC 50/60 Hz (AC-3e)
Motor Power Hp	3 hp at 115 V AC 50/60 Hz for 1 phase motors
	7.5 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	15 hp at 200/208 V AC 50/60 Hz for 3 phases motors
	15 hp at 230/240 V AC 50/60 Hz for 3 phases motors
	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors
	40 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit
Thermal Current	80 A (at 60 °C) for power circuit

Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
	900 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	900 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	400 A 40 °C - 10 s for power circuit
Current	810 A 40 °C - 1 s for power circuit
	84 A 40 °C - 10 min for power circuit
	208 A 40 °C - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	100 A gG at <= 690 V coordination type 1 for power circuit
	100 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	3.7 W AC-3
	9.6 W AC-1
	3.7 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
	Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
,	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.45 Mcycles 50 A AC-3 at Ue <= 440 V
	1.1 Mcycles 80 A AC-1 at Ue <= 440 V
	1.45 Mcycles 50 A AC-3e at Ue <= 440 V
Control Circuit Type	AC at 60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 60 Hz
	0.851.1 Uc (-4060 °C):operational AC 60 Hz
	11.1 Uc (6070 °C):operational AC 60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	45 W at 60 Hz
Operating Time	419 ms opening
	1226 ms closing
Maximum Operating Rate	3600 cyc/h 60 °C
	0000 0juii 00 0

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without
	cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable
	end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without
	cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without
	cable end Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness; flexible
	without cable end
	Power circuit: EverLink BTR screw connectors 2 125 mm ² - cable stiffness: flexible without cable end
	Power circuit: EverLink BTR screw connectors 1 135 mm ² - cable stiffness: flexible with cable end
	Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: flexible with cable end
	Power circuit: EverLink BTR screw connectors 1 135 mm² - cable stiffness: solid without cable end
	Power circuit: EverLink BTR screw connectors 2 125 mm² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver flat Ø
	6 mm Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver
	Philips No 2 Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm²
	hexagonal screw head 4 mm Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm²
	hexagonal screw head 4 mm Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver
	pozidriv No 2
	Power circuit: 2.5 N.m - on EverLink BTR screw connectors - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact1.5 ms on energisation between NC and NO contact
Mounting Support	Plate Rail
Environment	
Standards	CSA C22.2 No 14 EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1 UL 508
	IEC 60335-1
Product Certifications	DNV GL
	UL
	BV
	CCC
	RINA GOST
	LROS (Lloyds register of shipping) CSA
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
	-

Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (10 Gn for 11 ms)
Height	122 mm
Width	55 mm
Depth	120 mm
Net Weight	0.855 kg

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.2 cm
Package 1 Width	13.7 cm
Package 1 Length	15.2 cm
Package 1 Weight	942.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.875 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	160
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	166.98 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
②	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
②	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information