

Lista sa podacima o proizvodima

Specifikacije



plavi svetlosni blok sa montažnim ramom - integrisan LED 24V

ZB5AVB6

❗ Obustavljeno: 2. 12. 2022.

❗ Kraj radnog veka: 31. 12. 2022.

❗ Nije u prodaji

Osnovne informacije

Grupa Proizvoda	Harmony XB5
Tip Proizvoda Ili Komponente	Kompletno telo/svetleći blok
Kratko Ime Uređaja	ZB5
Materijal Montažnog Rama	Plastika
Prodaja Po Nedeljivim Količinama	1
Povezivanje - Priklučci	Vijčani priključni blokovi, <= 2 x 1.5 mm ² sa kablovskim završetkom u skladu sa EN 60947-1 Vijčani priključni blokovi, >= 1 x 0.22 mm ² bez kablovskog završetka u skladu sa EN 60947-1
Svetlosni Izvor	Zaštićeni LED
Baza Sijalice	Integrisan LED
Boja Svetlosnog Izvora	Plava

Dopunske informacije

Cad Ukupna Širina	30 mm
Cad Ukupna Visina	42 mm
Cad Ukupna Dubina	32 mm
Opis Priključaka Iso N°1	(X1-X2)PL
Masa Proizvoda	0,022 kg
Moment Pritezanja	0,8...1,2 N.m u skladu sa EN 60947-1
Oblik Glave Zavrtnja	Ukrštena kompatibilno sa Philips no 1 odvijač Ukrštena kompatibilno sa pozidriv No 1 odvijač Sa prerezom kompatibilno sa matica Ø 4 mm odvijač Sa prerezom kompatibilno sa matica Ø 5.5 mm odvijač
[Ui] Nazivni Napon Izolacije	600 V (stepen zaprljanosti 3) u skladu sa EN 60947-1
[Uimp] Nazivni Podnosivi Impulsni Napon	6 kV u skladu sa EN 60947-1
Tip Signalizacije	Trajna
[Us] Nazivni Napon	24 V AC/DC pri 50/60 Hz
Granice Napona	19,2...30 V DC 21,6...26,4 V AC
Struja Potrošnje	18 mA
Servisni Vek	100000 sati pri nazivnom naponu i 25 °C
Podnosivi Naponski Udar	1 kV u skladu sa IEC 61000-4-5

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Prezentacija Uređaja	Osnovni delovi uređaja
----------------------	------------------------

Okruženje

Tretman Zaštite	TH
Temperatura Okoline Za Skladištenje	-40...70 °C
Temperatura Okoline Za Rad Uređaja	-40...70 °C
Klasa Zaštite Protiv Električnog Udara	Klasa II u skladu sa IEC 60536
Standardi	EN/IEC 60947-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 CSA C22.2 No 14 JIS C8201-5-1 UL 508 JIS C8201-1
Sertifikacija Proizvoda	GL BV DNV CSA LROS (Lloyds register of shipping) UL odobrenje
Otpornost Na Vibracije	5 gn (f= 2...500 Hz) u skladu sa IEC 60068-2-6
Otpornost Na Udare	30 gn (trajanje = 18 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27 50 gn (trajanje = 11 milisekundi) za ubrzanje polovine sinusne periode u skladu sa IEC 60068-2-27
Otpornost Na Brze Prelaze	2 kV u skladu sa IEC 61000-4-4
Otpornost Na Elektromagnetna Polja	10 V/m u skladu sa IEC 61000-4-3
Otpornost Na Elektrostatičko Pražnjenje	6 kV na kontaktu (metalnim delovima) u skladu sa IEC 61000-2-6 8 kV u vazduhu (u izolovanim delovima) u skladu sa IEC 61000-2-6
Elektromagnetna Emisija	Klasa B u skladu sa IEC 55011

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3,700 cm
Package 1 Width	5,300 cm
Package 1 Length	6,000 cm
Package 1 Weight	20,0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	200
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,484 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1600
Package 3 Height	75,000 cm
Package 3 Width	80,000 cm

Package 3 Length	60,000 cm
Package 3 Weight	43,872 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH


Performanse dobrobiti

✓ Bez Žive	
✓ Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka


Dimensions



Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
(3) Ø22.5 mm recommended ($\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$) / Ø0.89 in. recommended ($\text{Ø}0.88 \text{ in. } \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- (1) Diameter on finished panel or support
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
(3) Ø22.5 mm recommended ($\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$) / Ø0.89 in. recommended ($\text{Ø}0.88 \text{ in. } \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$)