

# Product data sheet

Specifications



## 56 Series, Switch, 10A 250V 1-Pole IP66, Chemical-Resistant Orange

PDL56SW110LERO

### Main

Range Of Product	56 Series™
Range	56 Series
Product Brand	Clipsal
Product Or Component Type	Rotary switch
Device Application	Control
Colour Tint	Orange
Motor M-Rating As3133	M50
Quantity Per Set	Set of 4
Type Of Packing	Carton

### Complementary

Number Of Poles	1
Control Type	Rotary
Material	PBT (polybutylene terephthalate)
Surface Finish	Gloss
Installation Direction	Vertical
Width	95 mm
Height	95 mm
Depth	62 mm
Rated Current	10A/10AX
[Ue] Rated Operational Voltage	240 V
Network Frequency	50 Hz
Network Number Of Phases	1 phase
Number Of Gangs	1 gang
Mounting Mode	Surface mounted
Fixing Center	84 x 84 mm
Cable Cross Section	0.75...6 mm <sup>2</sup>

### Environment

Ip Degree Of Protection	IP66
Ambient Air Temperature For Operation	-40...55 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	156 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations