

Product data sheet

Specifications



13A 250V - triple phase 3 pole - flat pin - IP66 (grey)

S56SO313GY

Main

Range	WPS
Device Short Name	56 series
Product Or Component Type	Socket-outlet
Colour Tint	Light grey

Complementary

Material	PVC (polyvinyl chloride) UV stabilised
Surface Finish	Gloss
Rated Current	13 A
[Ue] Rated Operational Voltage	250 V
Network Frequency	50 Hz
Network Number Of Phases	3 phases
Number Of Gangs	1 gang
Pin Number	3
Device Composition	Flat pin
Mounting Mode	Surface mounted

Environment

Ip Degree Of Protection	IP66
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	10.4 cm
Package 1 Length	10.5 cm
Package 1 Weight	500.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins